



used for:

MATERIAL:

INSULATOR : PBT +30% GLASS FIBER (UL 94V-0)
CONTACT : PHOSPHOR BRONZE
CONTACT FINISH : GOLD ON MATING END, TIN ON TERMINATION END,
WITH ENTIRE CONTACT NICKEL UNDERPLATED
SHELL : BRASS, NICKEL PLATED
BACK SHELL : STEEL, NICKEL PLATED
BOTTOM COVER : NYLON, BLACK

SPECIFICATION:

CURRENT RATING : 1.5AMP
DIELECTRIC WITHSTANDING VOLTAGE : 500V AC
INSULATION RESISTANCE : 1000MΩ MIN.
CONTACT RESISTANCE BEFORE : 30mΩ MAX
CONTACT RESISTANCE AFTER : 50mΩ MAX
OPERATING TEMPERATURE : -20°C ~ +85°C



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION									
DO NOT ALTER CAD DRAWING BY HAND									
tolerance		finish		scale:		SEE MATERIAL			
unless otherwise specified tolerance shall be as follow		name		title:		USB Connector A female type			
Decimal .xxx		date		draw.		PCB R/A (Triple)			
Angles:		May 09		appd.		Rohs compliant			
		May 09		norm		AutocAD 2005			
				d-old		drawing no.:			
						39K1A243			
						part no.:			
						33UBAR-TSNIR			
						DIN A3			
						sheet 1/1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CONEC:

33UBAR-TSN1R