

Command-type TFT-LCD Module

10.1 inch standard product

RoHS

■ Features

This TFT-LCD module/control board displays content, including stored JPEG images and text with internal fonts, by way of a simple command set.

■ Specifications


Item \ Series		LC010AZ
LCD panel	Display size class [inch]	10.1 (IPS type)
	Pixels [dot]	1280 × 800 (WXGA)
	Active area [W×H mm]	216.96 × 135.60
	Luminance [c/m ²]	250
	Viewing angles [deg]	Bottom = 85, Top = 85, Left = 85, Right = 85
	Backlight type	LED
	LED lifetime [h] ※1	min. 20,000
Interface		USB 2.0 Full Speed & RS232C (115.2 kbps max.)
Touch panel	Type	resistive
	Active area [W×H mm]	228.66 × 148.40
	Surface durability [touches]	1,000,000
	Surface hardness	3H
Character		Japanese
Font code		FA UD Gothic-R
Internal memory for screen images	Full screen JPEGs	50 Mb ※2
	Partial screen JPEGs	
Supply voltage [V]		12.0
Power consumption [W]		6.0
Operating temperature [°C]		-10 ~ +50
Storage temperature [°C]		-20 ~ +60
Operating temperature [%RH] no condensation		20 ~ 90
Storage temperature [%RH] no condensation		5 ~ 90
Outer dimension [W×H×T mm]		250 × 151.8 × 20.3
Weight [g]		approx. 600

※1: LED lifetime = hours for the module luminance to decrease to 50% of original measured brightness at Ta = 25°C.

※2: A max. of 50 Mb of JPEG images can be stored and does not depend on the number of the JPEGs.

i.e. 200 JPEGs @ 256Kb; 400 JPEGs @ 128 Kb; 800 JPEGs @ 64Kb

■ Appearance, outer dimensions



LC010AZ (with touch panel)

<Contact>

Futaba Corporation Makuhari Marketing & Sales Center Makuhari Techno-Garden B6, 1-3 Nakase, Mihama-ku, Chiba, 261-8555, Japan

TEL : 81-43-296-5112 FAX : 81-43-296-5122

URL <http://www.futaba.co.jp/>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Futaba:

LC101LA1RC