



opulent
americas



Luminus High Power Starboards

Industry Leading High Powered LED Starboards

Data Sheet

Version 1.0

Lean & Fast. Made Smarter.

Superior Performance – Stay current with the highest intensity LEDs

Design Faster – Use industry standard starboards to shorten development time

Maximum Flexibility – Design to your exact specifications using Opulent Americas' starboards


Rapid Innovation – Work with Opulent Americas on your custom solution

Primary Applications



Horticulture
Entertainment
Stage/concert
Spot lighting
Architectural

Canopy
Garage
Portable
High bay



Custom Solutions

Opulent Americas operates facilities globally with ISO certifications for the LED lighting, automotive and medical industries. Our North Carolina based office provides quick engineering & sales support with a R&D lab for prototype development and custom solutions. Our in-house global manufacturing capabilities allow for both building in the United States as well as overseas at scale.

About Opulent Americas

Opulent Americas accelerates the adoption of LED technology through simple, modular products and custom designs. Through 30 years of experience, state of the art manufacturing, full traceability and advanced quality controls, Opulent offers leading solid state lighting components, modules and custom solutions. Opulent customers get to market faster, with less resources, at lower costs. Visit opulent-americas.com for more information.

Luminus High Power Starboards

Product Selection Table


LED	Part Number	CCT	CRI	Luminous Flux (lm)		Efficacy Nominal (lm/W)	Watts (W)	
				Nominal 700mA	Max 3000mA		Nominal	Max
Warm CCT SST-20	LST1-01G03-2795-01	2700K	95	167	484	87	1.9	8.2
	LST1-01G03-3095-01	3000K	95	180	520	94	1.9	8.2
	LST1-01G03-3595-01	3500K	95	193	556	101	1.9	8.2
	LST1-01G03-4095-01	4000K	95	205	593	107	1.9	8.2
Cool CCT SST-20	LST1-01G03-5065-01	5000K	70	302	903	144	2.1	9.0
	LST1-01G03-5765-01	5700K	70	302	903	144	2.1	9.0
	LST1-01G03-6065-01	6000K	70	316	944	150	2.1	9.0
	LST1-01G03-6565-01	6500K	70	316	944	150	2.1	9.0

All values shown above are typical.
Do not look into the light that is emitting from these LEDs as it is harmful to the human eye.
Eye injury may result. Use skin and eye protection as necessary.

Maximum Ratings

Part Number	DC Current (A)	Forward Voltage (V)	Tsp Temp (°C)	Power (W)
LST1-01G03-x (2700K - 4000K)	3.0	3.1	105	8.2
LST1-01G03-x (5000K - 6500K)	3.0	3.3	105	8.0

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

New Energy:

[LST1-01G03-2795-00](#) [LST1-01G03-3095-00](#) [LST1-01G03-3595-00](#) [LST1-01G03-4095-00](#) [LST1-01G03-5070-00](#)
[LST1-01G03-5770-00](#) [LST1-01G03-6070-00](#) [LST1-01G03-6570-00](#) [LST1-01G03-2795-01](#) [LST1-01G03-3095-01](#)
[LST1-01G03-3595-01](#) [LST1-01G03-4095-01](#) [LST1-01G03-5070-01](#) [LST1-01G03-5770-01](#) [LST1-01G03-6070-01](#)
[LST1-01G03-6570-01](#)