SMT POWER INDUCTORS

Toroid Series Ruggedized



- ۲ Ruggedized header with SLED rails for secure board mounting
- Current Rating: up to 3.8ADC ۲
- Inductance Range: 9.4µH to 439µH ۲
- Moisture Sensitivity Level: 1 Ô

Electrical Specifications @ 25°C – Operating Temperature -40 °C to $+130$ °C								
Part ⁹ Number	Inductance @ Irated (µH)	Irated (A)	DCR (mΩ)		ET	Inductance	100 Gauss	1 Amp DC
			ТҮР	MAX	(V-µsec)	(µH ±10%)	(V-µsec)	H I (Orsted)
PL8500	9.4	3.80	27	32	15.2	10.4	2.65	11.95
PL8501	13.3	3.20	40	46	18.8	14.6	3.13	14.12
PL8502	23	2.40	65	74	24.3	25	4.10	18.46
PL8503	50	1.60	121	135	37.0	56	6.15	27.69
PL8504	75	1.30	181	220	44.3	83	7.47	33.67
PL8505	90	1.20	246	285	49.2	100	8.19	36.93
PL8506	137	1.00	387	425	59.4	152	10.12	45.61
PL8507	200	0.82	585	673	71.3	220	12.17	54.85
PL8508	305	0.66	845	972	85.8	331	14.94	67.34
PL8509	439	0.56	1322	1520	99.6	472	17.83	80.37

NOTES: 1. The reference inductance at rated DC current is a typical value.

2. Temperature rise is 50°C in typical buck or boost circuits at 250kHz and with the reference ET applied to the inductor.

3. Total loss in the inductor is 380mW for 50°C temperature rise above ambient.

4. To estimate temperature rise in a given application, determine copper and core losses, divide by 380 and multiply by 50.

- For the copper loss, calculate IDC^2 X RN. For core loss, using frequency (f) and operating flux density (B), 5. 6. calculate 6.11 x 10⁻¹⁸ x B^{2.7} x f^{2.04}.

- 7. For flux density (B), calculate ET (V-µsec) for the application, divide by ET100 from the table, and multiply by 100.
- 8. Limit the DC bias (H) to 46 orsteds. Calculate H by multiplying H1 from the table by IDC of the application.
- 9. Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. PL8500 becomes PL8500T).



Mechanical



Electrical Schematic



Pan & Tube	
Tape & Reel	
MSL	
Dimensions: Inches mm	
Unless otherwise specified,	





www.inrcore.com

SMT POWER INDUCTORS

Toroid Series Ruggedized



T _{SMIN} (°C)	T _{SMAX} (°C)	T _L (°C)	T₽ (°C MAX)	ts (s)	t _L (s)	t _P (s MAX)	Ramp-up rate (T _L to T _P)	Ramp-down rate (T _P to T _L)	Time 25°C to peak temperature (s MAX)	
100	100 150 183 235 6		60-120	60-150	20	3°C/s MAX	6°C/s MAX	360		

Notes:

1. All temperatures measured on the package leads.

2. Maximum times of reflow cycle: 2.

For More Information

iNRCORE,LLC 311 Sinclair Road Bristol, PA 19007-6812 U.S.A Tel: + 1.215.781.6400 Fax: +1.215.7816430

Global Sales Representatives and Locations: http://www.inrcore.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2020. iNRCORE, LLC. All rights reserved.



www.inrcore.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

 INRCORE:

 PL8502
 PL8502NL
 PL8502T