

Wireless Hi Power Transmitter Module (RF ASK)

**Version History**

Version	Date	Changes
V1.01	Mar. 01, 2002	1 st . Edition
V1.02	Jul. 05, 2008	2 nd . Edition
V1.03	Oct. 20, 2010	3 nd . Edition

Model : TWS-BS-3

- Frequency Range: 433.92MHz
- Modulate Mode: ASK
- Circuit Shape: SAW
- Data Rate: 8Kbps
- Supply Voltage: 1.5~12V
- Output Power : 14dBm
- Working temperature: -20~+85℃
- Solder temperature: 230℃(10 seconds).
- High sensitivity is designed.

Application

● Wireless Data Transmission	● Wireless Game Pad
● Remote Control	● Wireless Toys
● Car Key	● Home Automation
● AMR- Automatic Meter Reading	● Remote Keyless Entry

Absolute Maximum Rating

Rating	Value	Unit
Power Supply and All Input/ Output Pins	-0.3~+12.0	V
Non-Operating Case Temperature	-20~+85	℃
Soldering Temperature(10 seconds)	230	℃

Electrical Characteristic


Characteristic	Min	Type	Max	Unit
Operating Frequency ($\pm 250\text{KHz}$)	433.67	433.92	434.17	MHz
Data Rate			8	Kbps
Current Consumption			8	mA
Output Power			32	mW
Operating Voltage	3		12	Vdc
Operating Ambient Temperature	-20		+85	°C

Pin Assignment

Pin	Function
1	GND
2	Data in
3	Vcc
4	ANT



Size



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SparkFun Electronics:](#)

[WRL-10534](#)