



APPROVAL SHEET

承认书

NS P/N	: EP-CHUPSMTVBPLX
MODEL NO.	: UP2 CASE-2 (荷兰 AN)
VERSION	: 01
DATE	: AUG. 27, 2018
PREPARED BY	: LI XIN
CHECKED BY	: SHEN LIHE
APPROVAL	: YAO JIARUI

BEIJING DEEPCOOL INDUSTRIES CO.,LTD

Building 10, No.9 Dijin Road, Zhongguancun Environmental Protection Park, Haidian Dist.
Beijing 100095, China

TEL: +86-10-5640 1752

FAX: +86-10-5640 1925

<http://www.deepcool.com>



MODIFICATION	VER	DATE



CONTENTS

1. COMPONENTS LIST , DESCRIPTION & PHOTO OF PRODUCT	3
1.1 COMPONENTS LIST	3
1.2 DESCRIPTION & PHOTO OF PRODUCT	4
2. CHARACTERISTICS	4
2.1 MECHANICAL CHARACTERISTICS.....	4
3. DRAWINGS: UP2 CASE-2 ASSEMBLY.....	5
3.1 LOGO PLATE	6
3.2 TOP COVER.....	7
3.3 MID-CASE	8
3.4 BASE PLATE	9
3.5 HOLDER	10
3.6 SCREW.....	11
3.7 NUT	12



1. COMPONENTS LIST, DESCRIPTION & PHOTO OF PRODUCT

1.1 COMPONENTS LIST

NO.	PART	SPEC/mm	QTY.	PAGE
1	LOGO PLATE	93.2X48X20.5	1	6
2	TOP COVER	98.5X93.5X23.4	1	7
3	MID-CASE	105X100X45	1	8
4	BASE PLATE	104X99X5.4	1	9
5	HOLDER	120X65X2	1	10
6	SCREW	M2.5X6KM	14	11
7	NUT	M2.5XH4X33	4	12
8	GAP PAD 1	33.0X26.0X0.5	1	/
9	GAP PAD 2	10X10X1.5	2	/
10	PAD 1	20X9X2	1	/
11	PAD 2	21X14X1	1	/
12	PAD 3	85X33X1	1	/
13	PLUG 1	φ 5.0Xφ 6.5X9	4	/
14	PLUG 2	φ 9.5Xφ 3.3X5.5	2	/



1. DESCRIPTION & PHOTO OF PRODUCT




View

2. CHARACTERISTICS

2.1 MECHANICAL CHARACTERISTICS


Overall Dimension	132.5X120X58.4
-------------------	----------------

3. DRAWINGS: UP2 CASE-2 ASSEMBLY



3.1 LOGO PLATE

GP




Tolerance as below, unless otherwise specified													
DIMENSION		0.5~3		>3~6		>6~30		>30~120		>120~400		>400~1000	
TOLERANCE		±0.1		±0.1		±0.2		±0.3		±0.5		±0.8	
			DESIGN			MATERIAL	AL1050	SCALE	1:1				
			PREPARED	LI XIN	2018/08/24	MATERIAL CODE	1.01.050.4840	PAGE	1/1				
			CHECKED			P/N	LOGO PLATE	UP2-1					
			APPROVAL			DWG.NO.	1.01.050.4840						
MODIFICATION	VER	NAME	DATE	BEIJING DEEPCOOL INDUSTRIES CO., LTD									


Notes:

- 1、Critical dimensions are marked with ★
- 2、Free from burrs and sharp edges.

3.2 TOP COVER




3.3 MID-CASE






3.4 BASE PLATE






3.5 HOLDER





3.6 SCREW


GP



Tolerance as below, unless otherwise specified									
DIMENSION	0.5~3	>3~6	>6~30	>30~120	>120~400	>400~1000	DESIGN	MATERIAL	SCALE
TOLERANCE	+0.1	±0.1	±0.2	±0.3	±0.5	±0.8	PREPARED	SEA1018	5:1
							LI XIN 2017/8/4	MATERIAL CODE	PAGE
							CHECKED	P/N	1/1
							APPROVAL	SCREW M2.5X6KM	
								DWG. NO.	
MODIFICATION	VER	NAME	DATE	BEIJING DEEPCOOL INDUSTRIES CO., LTD					

3.7 NUT

GP



Tolerance as below, unless otherwise specified						
DIMENSION	0.5~3	>3~6	>6~30	>30~120	>120~400	>400~1000
TOLERANCE	±0.1	±0.1	±0.2	±0.3	±0.5	±0.8
	DESIGN			MATERIAL	CU	3:1
	PREPARED	LI XIN	2018/8/16	MATERIAL CODE		PAGE 1
	CHECKED			P/N	NUT M2.5XH4X33	
	APPROVAL			DWG.NO.		
MODIFICATION	VER	NAME	DATE	BEIJING DEEPCOOL INDUSTRIES CO., LTD		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[AAEON:](#)

[EP-CHUPSMTVBPLX](#)