



CRYSTEK
CRYSTALS
A DIVISION OF CRYSTEK CORPORATION

CCLD-033 Model
5×7 mm SMD, 3.3V, LVDS

CCLD-033 5×7mm SMD LVDS Clock Oscillator



Model CCLD-033 is a 77.760 MHz to 161.000 MHz LVDS Clock Oscillator operating at 3.3 Volts. The oscillator utilizes a High Q Third Overtone crystal design providing very low Jitter and Phase Noise. No Sub-Harmonics are present in the Output Signal.



5×7mm SMD

Applications:

**Digital Video
SONET/SDH/DWDM
Storage Area Networks
Broadband Access
Ethernet, Gigabit Ethernet**

Rev: S
Date: 26-Aug-2021
Page 1 of 3



CRYSTEK
CORPORATION

16850 ORIDLE ROAD • FORT MYERS, FLORIDA 33912
PHONE: 239-561-3311 • 800-237-3061
WWW.CRYSTEK.COM



CCLD-033 5×7mm SMD LVDS Clock Oscillator



CCLD-033 Model

5×7 mm SMD, 3.3V, LVDS

Frequency Range:
Frequency Stability Options(ppm):
Temperature Range:
(Option M)
(Option X)
Storage:
Input Voltage:
Input Current:
Standby Current:
Output:
Symmetry:
Rise/Fall Time:
Load:
Output Drive Capability (see Note 1):
Logic:
Output Voltage Levels

Differential Output Voltage:
Disable Time:
Start-up Time:
Phase Jitter: 12kHz~80MHz
Phase Noise: (See Plot Below)
Sub-harmonics:
Aging:


77.760 MHz to 161.000 MHz
±20, ±25, ±50, ±100
(standard) 0°C to +70°C
-20°C to +70°C
-40°C to +85°C
-45°C to 90°C
3.3V ± 0.3V
66mA Max
30uA Max
Differential LVDS
45/55% Max @ zero crossing point
1ns Max (20% to 80%)
100 Ohms Connected between OUT and COUT
Zero Impedance Bipolar Process

“0”=0.90 Min, 1.10 Typical
“1”=1.43 Typical, 1.60 Max
247mV Min, 454mV Max
200ns Max
10ms Max
0.5ps Typical, 1ps RMS Max

None
<3ppm 1st year, <1ppm every year thereafter

Note 1:

Internal Driver will change to Finite Impedance CMOS Process. Consult factory for additional details and changeover date.



Rev: S

Date: 26-Aug-2021

Page 2 of 3





CCLD-033 5×7mm SMD LVDS Clock Oscillator

CCLD-033 Model
5×7 mm SMD, 3.3V, LVDS



Crystek Part Number Guide

CCLD - 033 X - 50 - 155.520

#1 #2 #3 #4 #5

#1 Crystek LVDS Osc.
#2 Model 033
#3 Temp Range: Blank = 0/70°C, M = -20/70°C, X = -40/85°C
#4 Stability: (see Table 1)
#5 Frequency in MHz: 3 or 6 decimal places

Example:
CCLD-033X-50-155.520
3.3V, -40/85°C, ±50ppm, 155.520 MHz

Stability Indicator

Blank	± 100ppm
50	± 50ppm
25	± 25ppm
20*	± 20ppm

*not available in -40/85

Table 1



Mechanical:

Shock: MIL-STD-883, Method 2002, Condition B
Solderability: MIL-STD-883, Method 2003
Vibration: MIL-STD-883, Method 2007, Condition A
Solvent Resistance: MIL-STD-202, Method 215
Resistance to Soldering Heat: MIL-STD-202, Method 210, Condition I or J


Environmental:

Thermal Shock: MIL-STD-883, Method 1011, Condition A
Moisture Resistance: MIL-STD-883, Method 1004


RECOMMENDED REFLOW SOLDERING PROFILE




Dimensions inches (mm)
All dimensions are Max unless otherwise specified.



Enable/Disable	
Function pin 1	Output pin
Open or N/C "1" level 0.7×Vdd Min "0" level 0.3×Vdd Max	Active Active High Z



SUGGESTED PAD LAYOUT



0.01µF Bypass Capacitor Recommended

PIN	Connection
1	Enable/Disable
2	N/C
3	GND
4	Output
5	Comp Output
6	Vcc

Rev: S

Date: 26-Aug-2021

Page 3 of 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crystek:](#)

[CCLD-033-50-133.000](#) [CCLD-033-50-125.000](#) [CCLD-033-50-100.000](#) [CCLD-033-50-156.25](#) [CCLD-033X-25-156.250](#)