

CCPD-033 5×7mm SMD LVPECL Clock Oscillator

CCPD-033 Model
5×7 mm SMD, 3.3V, LVPECL



Model CCPD-033 is a 77.760 MHz to 161.132800 MHz LVPECL Clock Oscillator operating at 3.3 Volts. The oscillator utilizes a High Q Third Overtone crystal design providing very low Jitter and Phase Noise. No Sub-Harmonics are present in the Output Signal.



5×7mm SMD

Applications:

**Digital Video
SONET/SDH/DWDM
Storage Area Networks
Broadband Access
Ethernet, Gigabit Ethernet**

Rev: X
Date: 19-Jan-2017
Page 1 of 3




CCPD-033 5×7mm SMD LVPECL Clock Oscillator



CCPD-033 Model

5×7 mm SMD, 3.3V, LVPECL

Frequency Range:	77.760 MHz to 161.132800 MHz
Frequency Stability Options(ppm):	±20, ±25, ±50, ±100
Temperature Range:	(standard) 0°C to +70°C
(Option M)	-20°C to +70°C
(Option X)	-40°C to +85°C
Storage:	-45°C to 90°C
Input Voltage:	3.3V ± 0.3V
Input Current:	55mA Typical, 88mA Max
Standby Current:	30uA Max
Output:	Differential LVPECL
Symmetry:	45/55% Max @ zero crossing point
Rise/Fall Time:	1ns Max (20% to 80%)
Logic: Terminated to Vdd-2V into 50 Ω	
Temp. 0°C to 85°C	"0"=1.490 Min, 1.680 Max
	"1"=2.275 Min, 2.420 Max
Temp. -40°C to 0°C	"0"=1.470 Min, 1.745 Max
	"1"=2.215 Min, 2.420 Max
Disable Time:	200ns Max
Start-up Time:	2ms Max
Phase Jitter: 12kHz~80MHz	0.5ps Typical, 1ps RMS Max
Phase Noise: (See Plot Below)	
Sub-harmonics:	None
Aging:	<3ppm 1 st year, <1ppm every year thereafter



Rev: X
Date: 19-Jan-2017
Page 2 of 3

Specifications subject to change without notice.





CCPD-033 5×7mm SMD LVPECL Clock Oscillator

CCPD-033 Model
5×7 mm SMD, 3.3V, LVPECL



Crystek Part Number Guide

CCPD - 033 X - 25 - 155.520

#1 #2 #3 #4 #5

#1 Crystek LVPECL Osc.
#2 Model 033
#3 Temp Range: Blank = 0/70°C, M = -20/70°C, X = -40/85°C
#4 Stability: (see Table 1)
#5 Frequency in MHz: 3 or 6 decimal places

Example:
CCPD-033X-25-155.520
3.3V, -40/85°C, ±25ppm, 155.520 MHz

Stability Indicator

Blank	± 100ppm
50	± 50ppm
25	± 25ppm
20*	± 20ppm

*not available in -40/85

Table 1


Mechanical:

Shock: MIL-STD-883, Method 2002, Condition B
Solderability: MIL-STD-883, Method 2003
Vibration: MIL-STD-883, Method 2007, Condition A
Solvent Resistance: MIL-STD-202, Method 215
Resistance to Soldering Heat: MIL-STD-202, Method 210, Condition I or J


Environmental:

Thermal Shock: MIL-STD-883, Method 1011, Condition A
Moisture Resistance: MIL-STD-883, Method 1004


RECOMMENDED REFLOW SOLDERING PROFILE




NOTE: Reflow Profile with 240°C peak also acceptable.




Dimensions inches (mm)
All dimensions are Max unless otherwise specified.



Enable/Disable	
Function pin 1	Output pin
Open or N/C	Active
"1" level 0.7×Vdd Min	Active
"0" level 0.3×Vdd Max	High Z



SUGGESTED PAD LAYOUT



0.01µF Bypass Capacitor Recommended

PIN	Connection
1	Enable/Disable
2	N/C
3	GND
4	Output
5	Comp Output
6	Vcc

Rev: X

Date: 19-Jan-2017

Page 3 of 3



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Crystek:

[CCPD-033-50-106.250](#) [CCPD-033X-25-156.25](#) [CCPD-033-50-156.250](#) [CCPD-033-50-161.1328](#) [CCPD-033X-25-106.25](#) [CCPD-033X-25-77.76](#) [CCPD-033-50-155.520](#) [CCPD-033-50-77.760](#) [CCPD-033X-25-161.1328](#) [CCPD-033X-25-155.52](#) [CCPD-033-50-100.000](#) [CCPD-033-50-125.000](#) [CCPD-033X-25-100](#) [CCPD-033X-25-125](#) [CCPD-033X-50-106.250](#) [CCPD-033X-50-125.000](#) [CCPD-033X-50-155.520](#) [CCPD-033X-50-156.250](#) [CCPD-033X-50-77.760](#) [CCPD-033X-50-100.000](#) [CCPD-033X-50-161.130](#) [CCPD-033-20-100.000](#) [CCPD-033X-50-161.1328](#) [CCPD-033X-25-155.520](#)