



CRYSTEK
MICROWAVE
A DIVISION OF CRYSTEK CORPORATION


High Pass Filter
50Ω SMA
7th Order



Part Number: CHPFL-0700



Schematic



Features:


- 7th Order Butterworth Response
- 50Ω SMA Connectors

Applications:

- Test Equipment
- Lab Use

Maximum Ratings:

- +36dBm (4 Watts)
- Operating Temperature: -40°C to 85°C
- Storage Temperature: -55°C to 100°C



Crystek's line of High Pass Filters are designed in a rugged SMA housing. This filter line has excellent out-of-band rejection. Designed for Test Equipment and General Lab Use.




Rev E

Page 1 of 3



CRYSTEK
CORPORATION

12730 COMMONWEALTH DRIVE • FORT MYERS, FLORIDA 33913
PHONE: 239-561-3311 • 800-237-3061
FAX: 239-561-1025 • WWW.CRYSTEK.COM





High Pass Filter CHPFL-0700

FREQ (MHz)	INSERTION LOSS (dB)	Male Return Loss (dB)	Female Return Loss (dB)
0.3	97.86	0.00	0.00
15.3	94.86	0.01	0.00
30.3	97.85	0.02	0.01
45.3	98.42	0.01	0.01
60.3	109.08	0.04	0.06
75.3	90.12	0.04	0.05
90.3	82.42	0.02	0.05
105	76.80	0.04	0.07
120	71.84	0.08	0.11
135	70.98	0.10	0.13
150	70.14	0.13	0.18
165	69.15	0.17	0.21
180	66.11	0.18	0.25
195	62.28	0.19	0.23
210	58.25	0.18	0.22
225	53.89	0.18	0.23
240	51.56	0.22	0.29
255	51.29	0.24	0.28
270	50.57	0.24	0.33
285	48.70	0.29	0.33
300	45.78	0.36	0.35
330	37.26	0.40	0.39
405	29.33	0.56	0.48
450	18.94	0.70	0.53
510	16.53	0.92	0.71
585	7.57	1.71	1.30
705	2.42	7.31	6.88
810	0.74	18.28	19.36
900	0.59	33.99	26.91
1005	0.63	20.65	18.06
1245	0.57	18.02	16.09
1500	0.46	20.53	18.56
1755	0.21	27.83	23.73
1995	0.27	33.87	33.63
2250	0.69	23.40	24.99
2505	0.50	19.31	19.25
2745	0.62	16.38	16.00
3000	0.80	14.07	13.53

Product Control:

Crystek Part Number:	CHPFL-0700	Release Date:	18-Aug-2015
Revision Level:	E	Responsible:	K. Piotrowicz

Rev E

Page 3 of 3



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crystek:](#)

[CHPFL-0700](#)