

Coaxial Cable Connector 16_QN-50-4-3/133_N

Description

Right angle cable plug

Interface standards
QN QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	11 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	29.5 dB	28 dB	20.5 dB

Mechanical Data

Centre contact	soldered
Outer contact	crimped

Environmental Data

Operating temperature	-40 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00079849
Assembly instruction	DOC-0000237514

Ordering Information

Bulk 100 pcs package	16_QN-50-4-3/133_NH
----------------------	---------------------

Additional Information

Suitable cables	S_04162_B-01, SX_04172_B-60, S_04262_B-01, Spuma_240-RS-FR, LMR-240, SPUMA_240-FR-01
-----------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[16_QN-50-4-3/133_NH](#)