

Coaxial Cable Connector 21_QMA-50-4-2/133_N

Description

Straight cable jack

Interface standards

QMA QLF compliant

Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	6 GHz		
Frequency range	DC to 2 GHz	2 to 4 GHz	4 to 6 GHz
Return loss	25 dB	20.2 dB	19.4 dB

Mechanical Data

Centre contact	plugged
Outer contact	crimped

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO / Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00153067
Assembly instruction	DOC-0000328446

Ordering Information

Bulk 100 pcs package	21_QMA-50-4-2/133_NH
----------------------	----------------------

Additional Information

Suitable cables	SX_04272_D-02, S_04272_B, S_04262_D, LMR-240
-----------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

21_QMA-50-4-2/133_NH