

## Coaxial Cable Connector 24\_BMA-N50-2-20/11-\_N

### Description

Straight bulkhead cable feed through

Interface standards

IEC 60169-33\_MIL-STD-348/321 fully intermateable

### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

#### Mechanical Data

Centre contact	plugged
Outer contact	soldered

#### Environmental Data

Operating temperature	-65 °C to 125 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00130440
Assembly instruction	DOC-0000230377
Mounting hole	DOU-00008950

### Ordering Information

Single package	24_BMA-N50-2-20/11-_NE
----------------	------------------------

### Additional Information

Suitable cables	EZ_86_TP_M17
-----------------	--------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[24\\_BMA-N50-2-20/11-\\_NE](#)