



CRYSTEK
MICROWAVE
A DIVISION OF CRYSTEK CORPORATION

Low Pass Filter
50Ω SMA
7th Order




Part Number: CLPFL-0400

Low Pass Range
DC to 400 MHz



Schematic



Features:


- 7th Order Butterworth Response
- 50Ω SMA Connectors

Applications:

- Test Equipment
- Lab Use

Maximum Ratings:

- +36dBm (4 Watts)
- Operating Temperature: -40°C to 85°C
- Storage Temperature: -55°C to 100°C



Crystek's new line of Low Pass Filters are designed in a rugged SMA housing. This filter line has excellent out-of-band rejection. Designed for Test Equipment and General Lab Use.

Rev C

Page 1 of 3




CRYSTEK
CORPORATION


12730 COMMONWEALTH DRIVE • FORT MYERS, FLORIDA 33913
PHONE: 239-561-3311 • 800-237-3061
FAX: 239-561-1025 • WWW.CRYSTEK.COM




400 MHz Insertion Loss



Male Side Return Loss



Female Side Return Loss





FREQ (MHz)	INSERTION LOSS (dB)	Male Return Loss (dB)	Female Return Loss (dB)
0.3	0.07	43.80	44.12
15.3	0.07	38.55	39.01
30.3	0.14	35.01	35.40
45.3	0.15	32.87	33.19
60.3	0.16	31.63	32.28
75.3	0.20	30.87	31.57
90.3	0.19	30.52	31.32
105	0.24	30.34	31.47
120	0.25	30.59	32.13
135	0.27	30.84	33.11
150	0.30	31.93	34.43
165	0.29	32.78	36.50
180	0.32	33.36	38.72
195	0.37	33.01	36.22
210	0.34	31.48	33.14
225	0.42	29.34	29.94
240	0.39	26.83	27.23
255	0.44	24.65	24.73
270	0.49	22.65	22.76
285	0.54	20.83	20.90
300	0.59	19.21	19.21
330	0.65	16.30	16.34
405	1.27	10.20	10.29
450	2.41	6.98	6.99
510	4.63	3.54	3.60
585	11.28	1.39	1.56
705	23.76	0.54	0.57
810	34.75	0.39	0.15
900	47.49	0.21	-0.11
1005	54.08	0.21	-0.36
1245	44.51	0.04	-0.52
1500	44.63	0.04	-0.50
1755	44.87	0.09	-0.31
1995	45.47	0.16	-0.09
2250	46.52	0.25	0.15
2505	47.82	0.38	0.33
2745	49.36	0.55	0.43
3000	51.18	0.67	0.54

Product Control:

Crystek Part Number:	CLPFL-0400	Release Date:	04-Aug-2015
Revision Level:	C	Responsible:	K. Piotrowicz

Rev C

Page 3 of 3



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Crystek:](#)

[CLPFL-0400](#)