

Coaxial Cable Connector 24_BNC-75-2-6/133_N

Description

Straight bulkhead cable feed through

Interface standards

Interface compatible with IEC 61169-8



Technical Data

Electrical Data

Impedance	75 Ω
Interface frequency max.	1 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0162 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	SUCOPLATE (R) Plating
Washer	Bronze	SUCOPLATE (R) Plating
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00008937
Catalogue drawing	DCA-00008934
Assembly instruction	DOC-0000179123
Mounting hole	DOU-00008751

Ordering Information

Single package	24_BNC-75-2-6/133_NE
Bulk 100 pcs package	24_BNC-75-2-6/133_NH

Additional Information

Suitable cables	RG_179_B/U, ENVIROFLEX_179, RG_187_A/U
-----------------	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[24_BNC-75-2-6/133_NE](#)