

Coaxial Cable Connector 24_TNC-50-4-12/12-_N

Description

Straight panel cable jack, flange mount

Interface standards

IEC 60169-17_MIL-STD-348A/313_CECC 22200



Technical Data

Electrical Data

Impedance	50 Ω	
Interface frequency max.	11 GHz	
Frequency range	DC to 6 GHz	6 to 11 GHz
Return loss	24.9 dB	23.1 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped

Environmental Data

Operating temperature	-60 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Other body part	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	
Fastening nut	Brass	Nickel Plating
Washer	Bronze	Nickel Plating

Related Documents

Outline drawing	DOU-00329761
Assembly instruction	DOC-0000294172
Mounting hole	DOU-00008751

Ordering Information

Single package	24_TNC-50-4-12/12-_NE
----------------	-----------------------

Additional Information

Suitable cables	EACON_4C
-----------------	----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[24_TNC-50-4-12/12-_NE](#)