

Between Series Adaptor 32_4310-716-50-X2/133_W

Description

PIM Adaptor plug/plug
4.3-10 plug (male) / 7/16 plug (male)

Interface standards
Series 4.3-10 - IEC 61169-54
Series 7/16 - IEC 61169-4_CECC 22190_DIN 47223_VG 95250

Benefits

Low passive intermodulation (PIM) adaptor



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz
PIM, 3rd order intermodulation distortion (IMD) max.	Static -155 dBc at 2x 43 dBm / 20 W carrier

Mechanical Data

Number of matings	500
Weight	0.117 kg

Environmental Data

Operating temperature	-55 °C to 90 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Interface - 4.3-10 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Interface - 7/16 plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Brass	Gold Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00287206
-----------------	--------------

Ordering Information

Single package	32_4310-716-50-X2/133_WE
----------------	--------------------------

Remarks

PIM typ. -166 dBc at 2 x 20 W / 43 dBm

Between Series Adaptor 32_4310-716-50-X2/133_W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

32_4310-716-50-X2/133_WE