

Coaxial PCB Connector 81_SMP SL-S50-0-F1SP

Description

Straight PCB plug

Interface Standards
MIL-STD-348, MIL-PRF-31031, DSCC 06026



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 26.5 GHz

Mechanical Data

Weight 0.0009 kg

Environmental Data

Operating temperature -65 °C to 165 °C

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Insulator	PEEK (Polyether-etherketone)	

Related Documents

Ordering Information

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[81_SMPSL-S50-0-F1SP](#)