


## Coaxial PCB Connector 85\_MCX-50-0-16/111\_N

### Description

Right angle PCB jack

Interface Standards

IEC 60169-36\_CECC 22220



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	6 GHz

#### Mechanical Data

Board mounting type	through holes
Weight	0.0017 kg

#### Environmental Data

Operating temperature	-55 °C to 155 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing	DOU-00012853
Catalogue drawing	DCA-00012855

### Ordering Information

Tape and Reel package	85_MCX-50-0-16/111_NM
Bulk 100 pcs package	85_MCX-50-0-16/111_NH
Single package	85_MCX-50-0-16/111_NE

### Remarks

PCB connector with stand-offs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[85\\_MCX-50-0-16/111\\_NE](#)