


Coaxial PCB Connector  
85\_QMA-50-0-4/111\_N

Description

Right angle PCB jack

Interface Standards  
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	6 GHz

Mechanical Data

Board mounting type	through holes
Weight	0.0047 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium / Bronze	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PFA / PTFE	

Related Documents

Outline drawing	DOU-00013254
-----------------	--------------

Ordering Information

Bulk 100 pcs package	85_QMA-50-0-4/111_NH
----------------------	----------------------

Remarks

PCB connector with stand-offs

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

85\_QMA-50-0-4/111\_NH