

Flexible low noise cable G_01130_HT-12

Description

G: RF cables with PE dielectrics

Low-noise coax, 50 Ohm, 1 GHz, 85°C, ø2.95 mm, PVC jacket



Technical Data

Construction

	Material	Detail	Diameter
Centre conductor	Copper	Strand-07	0.45 mm
Dielectric	PE (Polyethylene)		1.4 mm
Semi conductor	PVC (Polyvinyl chloride)		1.9 mm
Outer conductor	Copper	Braid, 91 %	2.4 mm
Jacket	PVC (Polyvinyl chloride)	RAL 7030 - gr	2.95 mm +/- 0.1

Print: (no print)

Electrical Data

Impedance	50 Ω
Max. operating Frequency	1 GHz
Capacitance	101 pF/m
Insulation resistance	$\geq 1 \times 10^6 \text{ M}\Omega\text{m}$
Max. operating voltage	1.5 kV _{rms} (at sea level)
Test voltage	3 kV _{rms} (50 Hz/1 min)
Max. noise level	10 mV

Mechanical Data

Weight	1.3 kg/100 m
Bending Radius	static 15 mm
	repeated (for max. 50 bendings) 30 mm

Environmental Data

Temperature range	-25 °C... +85 °C
Installation temperature	-20 °C... +60 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Additional Information

Ordering Information

Order as	G_01130_HT-12
----------	---------------

Remarks

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Cable group	U3 2 mm / 50 Ohm
-------------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[G_01130_HT-12](#)