

Flexible low noise cable G_01130_HT

Description

G: RF cables with PE dielectrics

Low-noise coax, 50 Ohm, 1 GHz, 85°C, ø3.15 mm, PVC jacket



Technical Data

Construction

	Material	Detail	Diameter
Centre conductor	Copper	Wire	0.4 mm
Dielectric	PE (Polyethylene)		1.4 mm
Semi conductor	PVC (Polyvinyl chloride)		1.9 mm
Outer conductor	Copper	Braid, 91 %	2.4 mm
Jacket	PVC (Polyvinyl chloride)	RAL 9005 - bk	3.15 mm +/- 0.1

Print: HUBER+SUHNER G 01130 HT 50 Ohm (production order number)

Electrical Data

Impedance	50 Ω
Max. operating Frequency	1 GHz
Capacitance	101 pF/m
Velocity of signal propagation	66 %
Signal delay	5 ns/m
Insulation resistance	≥ 1 x 10 ⁸ MΩm
Max. operating voltage	1.5 kV _{rms} (at sea level)
Test voltage	3 kV _{rms} (50 Hz/1 min)
Max. noise level	10 mV

Mechanical Data

Weight	1.6 kg/100 m
Bending Radius	static 16 mm
	repeated (for max. 50 bendings) 32 mm

Environmental Data

Temperature range	-25 °C... +85 °C
Installation temperature	-20 °C... +60 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Additional Information

Ordering Information

Order as	G_01130_HT
----------	------------

Remarks

(For details refer to the HUBER+SUHNER RF CABLES GENERAL CATALOGUE or contact your nearest HUBER+SUHNER partner)

Cable group	U3 2 mm / 50 Ohm
-------------	------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

G_01130_HT