

SENCITY® Road PUCK Antenna K7023211

Description

Bus and Tram rooftop antenna for 406-428 MHz.



Product Configuration

Technical Data

Electrical Data

	Band 1	Band 2	Band 3
Frequency (MHz)	406 - 410	410 - 425	425 - 428
VSWR	1.9	1.7	1.9
Impedance (Ohm)	50	50	50
Ambient temperature (°C)	25	25	25

Ports

	Port 1
Port name	Tetra
Connector	N, jack (female)
Polarization	vertical
DC grounded	Yes

Connections

	Band 1	Band 2	Band 3
Port 1	X	X	X

General Data

Indicated VSWR values are valid for a metallic ground plane of 1M x 1M or larger.

Mechanical Data

Dimensions (mm)	70 x 110 (Height x Diameter)110 x 110 (Diameter x Length)70 x 110 x 110 (Height x Width x Depth)
Weight (kg)	0.4

Radiator and base: Aluminum.

Radome: High impact plastic.

All screws and nuts: Stainless steel.

All metall parts of this antenna are DC grounded.

Robust and car-wash proof vehicular antenna.

Packaging size (outside): 117 x 117 x 114 mm

Environmental Data

Environmental conditions	outdoor
Operation temperature (°C)	-40 to 85
Storage temperature (°C)	-55 to 85
IP rating	IP56

SENCITY® Road PUCK Antenna K7023211

Flammability rating	ECE-R118
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant
REACH 1907/2006/EC	compliant

ECE-R118 for rooftop installation only.

Material Data

Radome colour	grey
Back plate/base plate colour	black
Back plate/base plate material	Aluminium

Related Documents

Mounting instruction	DOC-0000864406
Painting instruction	DOC-0000256180
Security instruction	DOC-0000278984
Outline drawing	DOU-00394038
3D-model	DOC-0000864402

Additional Information

The drilling diameter is 12 mm except the N connector versions: 17 mm. A special zinc washer ensures a good contact at the edges of the hole.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[K7023211](#)