



MULTI-PORT Jumper

1 / 2


LIS-C5-11MQ5X-5x11N-XXXXX-53

Cable: 5x SUCOFEEED 1/4" HFX (High Flex, X = cross linked)

Connectors: 1x straight male MQ5X (screw / HEX. nut) and 5x straight male N

Multi Coax Assembly consisting of corrugated 1/4" high flex (X, cross linked) coaxial cable with connectors 1x straight male MQ5X and 5x straight male N for frequencies DC to 6 GHz.

Mechanical Diagram



Port Assignment

Port No.	Cable No.	Label Printing
1	X1	ANT 1
2	X2	ANT 2
3	X3	ANT 3
4	X4	ANT 4
5	X5	CAL

List of Components

Pos	Components	Description	Type
1	Cable type	Corrugated 1/4" High Flex cross linked with PE jacket	SUCOFEEED 1/4" HFX
2	Connector type	MQ5X straight male screw version	11_MQ4-50-5-X1
3	Connector type	N straight male (5x)	LIS11_N-50-5-STD
4,5	Marking	See Marking and Packing section	

Electrical Data (values per single cable)

Impedance		50 Ω	Frequency: 6 GHz (max. operating)							
Return loss	100% tested	Frequency	Up to 5m			Frequency		Up to 5m		
		DC - 1.00 GHz	≥ 28 dB			3.30 - 4.20 GHz		≥ 21 dB		
		1.70 - 2.20 GHz	≥ 26.5 dB			4.40 - 5.00 GHz		≥ 19 dB		
		2.20 - 2.70 GHz	≥ 25 dB			5.15 - 5.95 GHz		≥ 17 dB		
Intermodulation		IM3 (2x20W)	≤ -155 dBc (typical: -163 dBc) / at 1.8 GHz or alternative at 0.9 GHz							
<u>Max.</u> Attenuation (at 20°C)		Length	0.5 m	1.0 m	1.5 m	2.0 m	2.5 m	3.0 m	4.0 m	5.0 m
		DC ÷ 1.00 GHz	0.14 dB	0.25 dB	0.36 dB	0.47 dB	0.57 dB	0.68 dB	0.90 dB	1.12 dB
		up to 2.20 GHz	0.20 dB	0.37 dB	0.54 dB	0.71 dB	0.88 dB	1.05 dB	1.39 dB	1.73 dB
		up to 2.70 GHz	0.22 dB	0.41 dB	0.61 dB	0.80 dB	0.99 dB	1.18 dB	1.57 dB	1.95 dB
		up to 4.20 GHz	0.28 dB	0.53 dB	0.78 dB	1.03 dB	1.28 dB	1.53 dB	2.03 dB	2.53 dB
	up to 5.00 GHz	0.31 dB	0.59 dB	0.86 dB	1.14 dB	1.42 dB	1.70 dB	2.25 dB	2.81 dB	
	up to 5.95 GHz	0.34 dB	0.65 dB	0.96 dB	1.27 dB	1.58 dB	1.89 dB	2.50 dB	3.12 dB	
RF power		25°C (sea level)	150W @ 2GHz							

**MULTI-PORT Jumper**

2 / 2

LIS-C5-11MQ5X-5x11N-XXXXX-53

Cable: 5x SUCOFEED 1/4" HFX (High Flex, X = cross linked)

Connectors: 1x straight male MQ5X (screw / HEX. nut) and 5x straight male N

Mechanical Data

Cable length	REF. to REF. of connector interfaces	up to 2m: +/-10mm // up to 3m: +/-30mm
Coupling nut torque	MQ4X or MQ5X male connector (recommended) N male connector (recommended)	25 Nm 2 ... 3 Nm
Bending radius	Single // Repeated (20 times) Cable bending must start after the molded connector cable entry protection!	min. 25 mm // min. 50 mm

Environmental Data

Temperature range	Operating // Installation // Storage	-40° C to +105° C // -25° C to +60° C // -70° C to +85° C
Waterproof rate	IP68 (0.1 bar, 1 h, 20°C)	RoHS (2011/65/EU) / Lead free solder : compliant

Requirement of included components**MQ4X straight male connector (HEX. nut)**

Interface	MQ5 / Meet std. IEC 63138-3	Coupling nut: HEX. 32 mm
Material / Plating	Body: Brass / NiSn Nut: Brass / Ni or NiSn	Centre contact: CuBe / Silver Insulator PTFE

N straight male connector

Interface	N / Meet std. IEC 61169-16	Coupling nut: HEX. 19 mm
Material / Plating	Body: Brass / Silver or Trimetal Nut: Brass / Ni or Trimetal	Centre contact: Brass / Silver Insulator PTFE

Corrugated 1/4" HFX (High Flexible, cross linked) cable

Jacket	PEX, black (Polyethylene cross-linked)	Max. Φ 8.0 mm	UV resistance: compliant
--------	---	--------------------	--------------------------

Marking and Packing

Positioning Label	Main label (No. 4): 10 cm from moulding MQ4X Cable label (No.5): 5 cm from moulding of connector No. 3
Printing	Main Label: Manufacturer's trade name/mark // PO or Batch no. // Product item No. Labels on cables: according mechanical diagram (page 1)
Packing	1 Assembly in a plastic bag, with protection on connector interfaces

Ordering Information / Product Description

LIS-C5-11MQ5X-5x11N-XXXXX-53 / XXXXX = Length of assembly in millimeters

Example: LIS-C5-11MQ5X-5x11N-02000-53

Jumper cable made with connectors 1x straight male MQ5X and 5x straight male N using corrugated cross linked cable 1/4" high flex with length 2000 millimeters (6.5 ft.).

WAIVER!

It is exclusively in written agreements that we provide our customer with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully complied to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

Issued: 15/04/2021

Revision: B

uncontrolled copy**HUBER+SUHNER**RF Division
www.hubersuhner.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[LIS-C5X-11MQ5X-5x11N-00500-53](#) [LIS-C5X-11MQ5X-5x11N-01000-53](#) [LIS-C5X-11MQ5X-5x11N-01500-53](#) [LIS-C5X-11MQ5X-5x11N-02000-53](#) [LIS-C5X-11MQ5X-5x11N-02500-53](#) [LIS-C5X-11MQ5X-5x11N-03000-53](#) [LIS-C5X-11MQ5X-5x11N-04000-53](#) [LIS-C5X-11MQ5X-5x11N-05000-53](#)