

HUBER+SUHNER® DATA SHEET

Coaxial Panel Connector: 27_MCX-50-0-101/111_N

Rev.: A



Description

Right angle bulkhead receptacle jack

Interface standards
IEC 60169-36_CECC 22220

Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Weight 0.0026 kg

Environmental Data

Operating Temperature -55 °C to 155 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium / Bronze
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Fastening nut	Brass
Washer	Copper Beryllium / Bronze

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)
Gold Plating (Nickel underplated)

Related Documents

Outline drawing	DOU-00010046
Mounting hole	DOU-00008855

Ordering Information

Single package	27_MCX-50-0-101/111_NE
----------------	------------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

HUBER+SUHNER:

[27_MCX-50-0-101/111_NE](#)