

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 25\_BMA-50-2-3/119\_N

Rev.: D



### Description

Straight panel cable jack, flange mount

Interface Standards

IEC 60169-33\_MIL-STD-348A/321



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 18 GHz

#### Mechanical Data

Centre contact soldered  
Outer contact crimped  
Weight 0.0061 kg

#### Environmental Data

Operating Temperature -65 °C to 125 °C  
2002/95/EC (RoHS) compliant

#### Material Data

##### Piece Parts

Centre contact	Copper Beryllium / Brass
Outer contact	Copper Beryllium Alloy
Body	Stainless Steel
Insulator	PFA / PTFE
Crimp ferrule	Copper

##### Surface Plating

Gold Plating (Nickel underplated)  
Gold Plating (without Nickel underplating)

Nickel Plating

#### Related Documents

Catalogue drawing	DCA-00009062
Assembly instruction	DOC-0000184996
Mounting hole	DOU-00008816

#### Ordering Information

Single package 25\_BMA-50-2-3/119\_NE

#### Additional Information

Suitable cables RG\_316\_/U, RG\_188\_A/U, RG\_174\_/U

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
RF Technology  
9100 Herisau, Switzerland  
Phone +41 (0)71 353 41 11  
Fax +41 (0)71 353 45 90  
www.hubersuhner.com

**HUBER+SUHNER – Excellence in Connectivity Solutions**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[25\\_BMA-50-2-3/119\\_NE](#)