INDUSTRIAL THIN MINI-ITX

conga-IC97



- Highest Performance Thin Mini-ITX board
- 5th Generation Intel® Core™ Mobile SOC U-Processors
- Improved Graphics Performance up to GT3 HD6000
- Wide Range Power Input 12-24 Volt
- congatec embedded Board Controller Features

Formfactor	Industrial Thin-Mini-ITX | 170 x 170 mm
CPU	Intel® Core™ i7-5650U 2.2 GHz Dual Core Turbo Boost 3.2 GHz 4 MB Cache TDP 15W GT3 HD 6000 Intel® Core™ i5-5350U 1.8 GHz Dual Core Turbo Boost 2.9 GHz 3 MB Cache TDP 15W GT3 HD 6000 Intel® Core™ i3-5010U 2.1 GHz Dual Core 3 MB Cache TDP 15W HD 6000 Intel® Celeron® 3765U 1.9 GHz Dual Core 2 MB Cache TDP 10W HD Graphics Intel® Turbo Boost Technology | Intel® Hyper-Threading Technology (Intel® HT Technology) | Intel® Advanced Vector Extensions 2.0 (Intel® AVX2), Intel® Advanced Encryption Standard New Instructions (Intel® AES-NI) | Integrated dual channel memory controller | up to 25.6 GByte/sec. memory bandwidth | Integrated Intel® HD Graphics 6000 series with dynamic frequency up to 1.1 GHz | Intel® Clear Video HD Technology Intel® Virtualization Technology (Intel® VT) | Intel® Trusted Execution Technology (Intel® TXT) | Intel® Streaming SIMD Extensions 4.2 (Intel® SSE4.2) PCLMULQDQ Instruction | Intel® Secure Key | Intel® Transactional Synchronization Extensions (Intel® TSX)
DRAM Memory	Support for 2x SO DIMM Socket (dual channel DDR3L up to 1600 MT/s) | max. 16GB
Ethernet	Dual LAN Gbit / 100 Mbit / 10 Mbit; 1x Intel Gigabit Ethernet PHY i218LM (with AMT support); 1x Intel Gigabit Ethernet Controller i210/i211
Sound	High Definition Audio Interface | Realtek ALC 888S | 7.1-channel
Graphics	Next Generation Intel® HD Graphics with OpenCL 2.0 | OpenGL 4.X and DirectX11.1 support; up to three independent displays: DDI | DVI, DisplayPort 1.2; High performance hardware MPEG-2 decoding | WMV9 (VC-1) and H.264 (AVC) support Blu-ray support @ 40 MBit/s
Graphic Interfaces	1x 24-bit Dual Channel LVDS Interface or eDP (x4) and 2x DisplayPort
Internal Connectors	1x PCIe x4 Slot (Gen.2) | 1x Full/Half-size Mini PCIe Slot shared with PCIe x1 slot | 1x Full/Half-size Mini PCIe Slot (shared with mSATA) | 3x SATA (6G) | 1x mSATA (SATA-III; 600) | 1x SATA Power | 4x USB 2.0 | 1x LVDS (2x24 bit) | 1x Embedded DisplayPort (x4) | 1x Backlight (Power | control) | 1x Monitor OFF | 1x Surround | 1x Front Panel HD Audio | 1x Digital Microphone (SPDIF) | 1x Internal stereo speaker 1x Serial Port COM1 (opt. as ccTALK) | 1x Serial Port COM2 | 1x Feature connector - congatec custom (8 Bit General Purpose I/O) | 1x Frontpanel (Power Switch, LEDs, Reset) | 1x Intrusion (Case Open) | 1x FAN CPU | 1x FAN System | 1x internal power header (12-24V) | 1x opt. battery header signal + power (SBM3) | 1x opt. CEC | 1x opt. SIM Card Slot
congatec embedded Controller	Multi-Stage Watchdog | non-volatile User Data Storage | Manufacturing and Board Information | Board Statistics | BIOS Setup Data Backup I²C bus (fast mode | 400 kHz | multi-master) | Power Loss Control
External Connectors (Frontpanel)	2x DisplayPort dp++ | Audio In | Line Out | 2x LAN RJ45 | 4x USB 3.0/2.0 | 1x PCIe x4 (via extension card) | 1x DC-In (external input)
Embedded BIOS	AMI Aptio® 2.X (UEFI) BIOS; SM-BIOS | BIOS Update | Logo Boot | Quiet Boot | HDD Password
Security	The conga-IC97 can be optionally equipped with a discrete "Trusted Platform Module" (TPM 1.2 / 2.0). It is capable of calculating efficient hash and RSA algorithms with key lengths up to 2,048 bits and includes a real random number generator. Security sensitive applications such as gaming and e commerce will benefit also with improved authentication, integrity and confidence levels.
Power Specification	Power Management | ACPI S3/S4/DeepSx | Wake on time from S5 | Power Supply 12V - 24V | 2 x FAN (CPU | system) monitored & controlled
Operating Systems	Microsoft® Windows 10 |Microsoft® Windows 10 IoT Enterprise |Microsoft® Windows 8 | Microsoft® Windows 7 | Linux | Microsoft® Windows® 7/8 embedded Standard
Power Consumption	Typ. application: tbd. | see manual for full details
Temperature:	Operating: 0 .. +60°C
Humidity Operating:	Operating: 10 - 90% r. H. non cond.
Size	170 x 170 mm (6.7" x 6.7")

conga-IC97 | Connectors



conga-IC97 | Block diagram



conga-IC97 | Order Information

Article	PN	Description
conga-IC97/i7-5650U	052501	Thin Mini-ITX board based on 5th Gen Intel® Core™ i7-5650U dual core processor with 2.2GHz, 4MB L2 cache and 1600MT/s dual channel DDR3L SODIMM memory interface
conga-IC97/i5-5350U	052502	Thin Mini-ITX board based on 5th Gen Intel® Core™ i5-5350U dual core processor with 1.8GHz, 3MB L2 cache and 1600MT/s dual channel DDR3L SODIMM memory interface
conga-IC97/i3-5010U	052503	Thin Mini-ITX board based on 5th Gen Intel® Core™ i3-5010U dual core processor with 2.1GHz, 3MB L2 cache and 1600MT/s dual channel DDR3L SODIMM memory interface
conga-IC97/3765U	052504	Thin Mini-ITX board based on Intel® Celeron® 3765U dual core processor with 1.90GHz, 2MB L2 cache and 1600MT/s dual channel DDR3L SODIMM memory interface.

Accessories		
conga-IC87/CSA	052252	Active cooling solution for conga-IC97 and with 12V fan and Thin Mini-ITX height
conga-IC87/Retention Frame	052254	Retention frame for standard cooling (PN: 052252) for conga-IC97
conga-IC87/IO Shield-Standard	052256	IO shield for conga-IC97 with Standard Mini-ITX height
conga-IC87/IO Shield - Thin	052257	IO shield for conga-IC97 with Thin Mini-ITX height
DDR3L-SODIMM-1600 (2GB)	068755	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 2GB RAM
DDR3L-SODIMM-1600 (4GB)	068756	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 4GB RAM
DDR3L-SODIMM-1600 (8GB)	068757	DDR3L SODIMM memory module with 1600 MT/s (PC3L-12800S) and 8GB RAM
conga-Thin MITX/eDP to DP Adapter	052231	eDP to standard DisplayPort evaluation adapter for congatec Thin Mini-ITX boards
conga-Thin MITX/LVDS Adapter	052233	LVDS pin header evaluation adapter for congatec Thin Mini-ITX boards
PS65	10000145	65 Watt power supply, 19V, 3.42 A, plug 7.4x5.1x12.5mm
PS90	10000146	90 Watt power supply, 19V, 4.74 A, plug 7.4x5.1x12.5mm
cab-ThinMini-ITX-UART	14000121	UART cable with 9pin DSUB connector for congatec Thin Mini-ITX family
cab-ThinMini-ITX-eDP 1-1	14000129	eDP 1-1 cable for congatec Thin Mini-ITX family. Both sides are with 40pin ACES eDP connector plug.
cab-ThinMini-ITX-LVDS-OE	14000125	LVDS cable with open end for congatec Thin Mini-ITX family. Can be used also for eDP with open end.
cab-ThinMini-ITX-BKLT	14000127	Backlight cable for congatec Thin Mini-ITX family
cab-ThinMini-ITX-USB20-Single	14000122	Single USB 2.0 cable for congatec Thin Mini-ITX family
cab-ThinMini-ITX-USB20-Twin	14000123	Dual USB 2.0 cable for congatec Thin Mini-ITX family
SATA III cable 30cm, straigth/straight	48000029	SATA III cable with 30cm length, shielded, end connectors straigth/straight
SATA III cable 30cm, down/straight	48000030	SATA III cable with 30cm length, shielded, end connectors down/straight
cab-ThinMini-ITX-SATA-Power	14000120	SATA power cable for congatec Thin Mini-ITX family. One end 15 pin SATA connector to to 3x15 pin SATA connector
LE910 Mini PCIe		4G / LTE Mini PCI Express card
HE910 Mini PCIe		3G / UMTS / HSPA+ Mini PCI Express card
SSD 256		256 GByte Intel® SSD Pro 2500 Series (16nm, MLC)
SSD 128		128 GByte Intel® SSD Pro 2500 Series (16nm, MLC)

© 2021 congatec GmbH.
All rights reserved.

All data is for information purposes only. Although all the information contained within this document is carefully checked, no guarantee of correctness is implied or expressed. Product names, logos, brands, and other trademarks featured or referred are the property of their respective trademark holders. These trademark holders are not affiliated with congatec AG. Rev. Mar 25 2021 KF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

congatec:

conga-IC97/i3-5010U conga-IC97/3765U conga-IC97/i7-5650U conga-IC97/i5-5350U conga-IC97/CSA