

Standard Battery Pack Li-Ion

Rechargeable Smart Battery Pack Li-ion 锂离子电池 3.7V 2000mAh
 Model: R3720 100% 100% 100%
 Net Weight: 37g 1.3oz
 Gross Weight: 47g 1.6oz
 Input: 5V 1A
 Output: 5V 1A
 Charge Cycle: 500 cycles
 Input: 5V 1A
 Output: 5V 1A
 Charge Cycle: 500 cycles

Caution
 Do not short circuit or expose to fire.
 Do not disassemble or modify.
 Do not use in high temperature or high humidity environment.
 Do not use in high pressure or high vibration environment.
 Do not use in high magnetic field environment.
 Do not use in high speed or high acceleration environment.
 Do not use in high frequency or high power environment.
 Do not use in high voltage or high current environment.
 Do not use in high speed or high acceleration environment.
 Do not use in high frequency or high power environment.
 Do not use in high voltage or high current environment.

CE
 RoHS
 REACH
 FCC
 ENEC
 TUV
 GS
 CCC
 BSMI
 KCC
 VCCI
 NCC
 MIC
 MET
 SAA
 UKCA
 UKCA

Manufactured in Taiwan
 Designed in Germany
 Assembled in Taiwan



The RRC2130 is in use in more than 50 different industries in a variety of applications, such as ultrasound devices, patient monitors, IoT devices, and many more.

In total, we count more than 4000 design-ins for our standard batteries, which is why the safety and reliability of our products is unmatched.

Characteristics & Benefits of the RRC21xx series standard Li-Ion battery packs:

- Smart batteries with numerous features according to the SMBus specification
- State-of-the-art lithium-ion cells with the market's highest energy density
- High discharge performance
- JEITA charging profile optimization
- Numerous and redundant safety features
- Increased ESD protection up to 8.00kV
- Up to 80% of initial capacity after 800 cycles



Worldwide Approvals



No NRE



Fast Time-to-Market



Highest Safety



Highest Quality



Highest Performance




Worldwide Availability



No Obsolescence



Independent of Quantity



Extensive Accessories



Dual Sourcing Strategy



Design-In Support

Characteristics






General	
Delivery status battery capacity	<30%
Compliance information	IEC 62133 / CE / UL2054 / CAN ICES-003(B) / NMB-003(B) / FCC / UKCA / PSE / KC / BSMI / GOST-R / CMIM / CCC / RCM / BIS / TISI / UN 38.3 / RoHS / REACH
Operating temperature	0°C to 45°C (charge) -20°C to 60°C (discharge)
Storage temperature	-20°C to 50°C max. -20°C to 25°C recommended
Communication interface	SMBus
P/N	110088
	Each battery has an individual serial number (S/N), which is located on the hardpack label for tracking & traceability.

Electrical Parameters	
Nominal voltage	7.20V
Nominal capacity	4.17Ah
Initial impedance	<180mΩ @ 1kHz at 25°C
Max. charge current	2.70A
Max. charge voltage	8.40V
Max. discharge current	6.00A

Battery Dimensions	
Length	150.60mm +0.50/-0.50
Width	86.20mm +0.40/-0.40
Thickness	8.35mm +0.25/-0.25
Weight	172g
Contacts	+, +, C, D, T, -, -
Ingress protection	IP40

Safety Features	
CUV (Cell Under Voltage)	Protection against deep discharge
COV (Cell Over Voltage)	Protection against over charge
OTC (Over Temperature in Charge)	Protection against overheating while charging
OTD (Over Temperature in Discharge)	Protection against overheating during discharging
OCC (Over Current in Charge)	Protection against overcurrent while charging
OCD (Over Current in Discharge)	Protection against overcurrent during discharging
OL (Overload in Discharge)	Protection against overload during discharging
SCC (Short Circuit in Charge)	Protection against short circuits while charging
SCD (Short Circuit in Discharge)	Protection against short circuits during discharging

Recommended Accessories

Type		Product	P/N	Application
Standard Battery Charger		RRC-SMB-FPC	110083	40.00W standard battery charger for optimized charging process with external power supply for world-wide use.
Power Supply AC/DC		PS65	210919	External power supply (worldwide use) for embedded battery charger RRC-PMM20 or for mobile devices. Included in RRC-SMB-FPC.
AC Power Cable		US-Version EU-Version UK-Version AU-Version CN-Version	210950 210951 211333 211334 211959	Country-specific power cable for PS65.
Car Adapter DC/DC		RRC-SMB-CAR	110041	90.00W car adapter with USB charging port. Power supplying in cars and trucks for RRC-SMB-FPC, RRC-PMM20 or mobile devices
Battery Mating Connector		RRC-MC21-90-10 RRC-MC21-90-20	211268 211278	Mating Connector for standard smart batteries RRC2130, RRC2140. Available for 90° PCB mounting (top and edge).



Our special competence is the development of power solutions according to the concrete requirements of our customers. We offer both standardized as well as customized solutions for customer's applications, while guaranteeing the highest level of safety and reliability to all our products. As an international company with German roots, we have a worldwide market operation - where we provide our proven German engineering skills combined with our technical expertise and flexibility, which are necessary to meet the challenges of the growing global market.

Germany / HQ
RRC power solutions GmbH

Technologiepark 1
66424 Homburg / Saar

+49 6841 98090
sales@rrc-ps.com

USA
RRC power solutions Inc.

18340 Yorba Linda Blvd.,
107-437
Yorba Linda, CA 92886

+1 714 777 3604
usa@rrc-ps.com

Hong Kong
RRC power solutions Ltd.

S-V,6/F, Valiant Industrial
Centre 2-12
Au Pui Wan Street
Fo Tan, N.T., Hong Kong

+852 2376 0106
hkrrc@rrc-ps.cn

China
RRC power solutions Ltd.

Room 1306, C Building,
Tianan International
Building
Renmin South Road
Luohu District
Shenzhen 518021

+86 755 8374 1908
hkrrc@rrc-ps.cn

Vietnam
RRC Power Solutions
Company Ltd.

Block C, Lot CN4
Dinh Vu - Cat Hai Economic
Zone, Dong Hai 2 Ward
Hai An District, 180000
Hai Phong City

vietnam@rrc-ps.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[RRC Power Solutions:](#)

[RRC2130](#)