


ODU AMC[®] SERIES T RECEPTACLE FOR BACKSHELL, SHELL SIZE 12, IP6K9K, 18 CONTACTS, A (LIGHT BROWN) KEY




- **Part number** GBTAAT0-HM18SN-0000
- **Type of connector** Receptacle for backshell
- **Size** Shell size 12
- **Number of contacts** 18
- **Keying** A (light brown)
- **Cable diameter** 5 - 14.6 mm



DIMENSIONS:




POSITIONS: 18 positions



CODING: A



PANEL CUT OUT:



Contact Insert Description

| | |
|--------------------|------------------------------|
| Number of contacts | 18 |
| Contact type | Sockets |
| Contact diameter | 4 x 0.9 mm, 14 x 0.76 mm |
| Insulator material | PEEK |
| Wire cross section | 4x AWG 20-24, 14 x AWG 22-26 |
| Termination type | Crimp |
| Contact size | 4x #20MD, 14x #22D |

Reverse gender on request

ODU AMC[®] SERIES T RECEPTACLE FOR BACKSHELL, SHELL SIZE 12, IP6K9K, 18 CONTACTS, A (LIGHT BROWN) KEY



Technical information

| | | |
|--------------------------------|----------------------------|--|
| Nominal current single contact | 4x 7.5 A, 14x 5 A | IEC 60512-5-2:2002 (DIN EN 60512-5-2:2003) |
| Test voltage | 4x 1 kV AC, 14x 0.75 kV AC | EIA-364-20F:2019-02 |

All shown connectors are rated to a safety extra low voltage (SELV) of less than 50 V AC / 75 V DC, according to IEC 61140:2016 (VDE 0140-1:2016) Protection against electric shock - Common aspects for installation and equipment. In case other standards rule a specific use of the connector, the application specific safety criteria shall be considered first. In this context, lower voltage ratings may be valid. Warning: Danger to life for operating voltages above 50 V AC / 120 V DC!

Mechanical and Environmental data

| | |
|-----------------------|---------------|
| Degree of protection* | IP6K9K |
| Operating temperature | -65°C - 175°C |
| Mating cycles | 500 |
| *mated | |

Material and Surface Treatments

| | |
|---------|---------------------------------|
| Housing | Aluminum with tin-nickel finish |
| Contact | Cu-alloy with gold finish |

General information

All shown connectors are defined without breaking capacity (COC) according to IEC 61984:2008 (VDE 0627:2009).

The respective selected ODU connectors with data transfer functionality can transmit common data transmission such as HDMI[®] 2.0, USB[®] 3.2 Gen 1x1, FireWire[®] and eSATA[®], but they are not HDMI[®]-, USB[®]-, FireWire[®]- and eSATA[®]-standard connectors.

ODU reserves the right to make changes based on the current state of knowledge without prior notice without being obliged to provide replacement deliveries or refinements of older designs.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU USA:

[GBTAAT0-HM18SN-0000](#)