

K32B0C-P16NFG0-9000  
series\_b, type\_k3



General information

|                   |                     |
|-------------------|---------------------|
| Part number       | K32B0C-P16NFG0-9000 |
| Termination       | crimp               |
| Size              | 2                   |
| Locking principle | break , push        |
| Keying            | 0_key               |
| Cable Diameter    | cable_mini_90       |
| Cable outlet      | standard            |



CODING: 0°

POSITIONS: 16 Positions

DIMENSIONS:

Contact insert description

|                    |           |
|--------------------|-----------|
| Number of contacts | 16        |
| Contact type       | sockets   |
| Contact diameter   | 07mm      |
| Insulator material | peek      |
| Wire cross section | 22-26_awg |
| Termination        | crimp     |

reverse\_gender\_on\_request

Technical information

|                                          |          |               |
|------------------------------------------|----------|---------------|
| Max. creepage and air clearance distance | 06_mm    | 10_mm         |
| Nominal current single contact           | 075_a    | iec_60512_5_2 |
| Nominal current insert                   | 3,75 A   | vde_0298_4    |
| Test voltage                             | 09_kv_ac | sae_13441     |

safety\_text

Mechanical and environmental data

|                       |          |
|-----------------------|----------|
| Degree of protection* | ip68     |
| Operating temperature | 40_120_c |
| Mating cycles         | 5000     |

mated

Material and surface treatments

|         |               |
|---------|---------------|
| Housing | m_chrome      |
| Contact | cu_alloy_gold |

safety\_text\_2  
ul\_text  
illustrative\_text

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ODU:

[K32B0C-P16NFG0-9000](#)