


ISG Series



- Regulated Single Output
- SMD Package
- Industry Standard Pinout
- 1000 VDC Isolation
- Short Circuit Protection
- MTBF >3.5 Mhrs
- 3 Year Warranty

Specification

Input

- Input Voltage Range • Nominal $\pm 5\%$
- Input Reverse Voltage Protection • None

Output

- Output Voltage • See table
- Minimum Load • $10\%^{(2)}$
- Line Regulation • $\pm 0.25\%$
- Load Regulation • $\pm 1\%$, 10-100% load change
- Setpoint Accuracy • $\pm 3\%$ at 100% load
- Ripple & Noise • 100 mV pk-pk 20 MHz bandwidth
- Temperature Coefficient • $0.03\%/^{\circ}\text{C}$
- Short Circuit Protection • Continuous

General


- Efficiency • See table
- Isolation Voltage • 1000 VDC
- Isolation Resistance • $10^9 \Omega$
- Switching Frequency • 100 kHz typical at nominal input, full load
- MTBF • >3.5 Mhrs to MIL-HDBK-217F at 25 °C, GB

Environmental

- Operating Temperature • -40°C to $+85^{\circ}\text{C}$, derate from 100% load at 70°C to 60% load at 85°C
- Storage Temperature • -55°C to $+125^{\circ}\text{C}$
- Case Temperature • 100°C max
- Cooling • Convection-cooled
- Lead Temperature • 260°C , 0.06 in (1.5 mm) from case, 10 s


Input Voltage	Output Voltage	Output Current	Efficiency (typical)	Model Number ⁽⁶⁾
5 VDC	5 V	150 mA	68%	ISG0505A

Mechanical Details



Recommended footprint

Top view grid: 0.1 x 0.1 in (2.54 x 2.54 mm)



Pin	Standard
1	GND
2	Vin
4	0V
7	+Vo
3, 6, 8, 9	N.C.
5, 10	N.C.

N.C. Not connected

Notes

1. Operation at no load will not damage device but may not meet all specifications.
2. All dimensions in inches (mm)
3. Tolerance: ± 0.010 (± 0.25)
4. Weight: 0.003 lbs (1.7 g)
5. Pin tolerance: ± 0.004 (± 0.10 mm)
6. For optional tape & reel option add suffix -TR to the end of the p/n. Reel quantity = 500

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[XP Power:](#)

[ISG0505A](#) [ISG0505A-TR](#)