

A vertical bar on the left side of the page, consisting of an orange rectangle on top and a green rectangle below it.

SL-MIPI-LVDS-HDMI-CNV-11 Datasheet and Pinout

Rev. 20231030134549


Source URL: http://wiki.somlabs.com/index.php/SL-MIPI-LVDS-HDMI-CNV-11_Datasheet_and_Pinout

Table of Contents

General description	1
Features	2
Pictures	3
Ordering info	6
Operating ranges	7
Electrical parameters	8
MIPI-DSI (input) Pinout	9
LVDS (output) Pinout	11
HDMI (output) Pinout	13
Dimensions	14

SL-MIPI-LVDS-HDMI-CNV MIPI-DSI to LVDS and HDMI converter Datasheet and Pinout

General description






SL-MIPI-LVDS-HDMI-CNV (MIPI-DSI to LVDS HDMI converter) is flexible MIPI-DSI to LVDS and/or HDMI converter. The solution we dedicate to SoMLabs carrier boards equipped with MIPI-DSI interface (with FPC30 connector). Converter is fully compliant with DSI1.02 and HDMI1.4 and converts video stream up to 1080p @60Hz/8b. SL-MIPI-LVDS-HDMI-CNV is fully compatible with SoMLabs carrier boards equipped with MIPI-DSI FPC30 connector.


Features

- MIPI-DSI to LVDS and/or HDMI display converter
- Integrated D-PHY1.1 (DSI1.02)
- From 1 up to 4 MIPI input data lanes
- Compatible with MIPI-DSI data packets: 18bpp, RGB666 and 24bpp RGB888
- Input bandwidth up to 6Gb/s (4 lanes)
- LVDS output clocking up to 154 MHz
- Fully compatible with SoMLabs carrier board:
 - VisionCB-8M-STD (dedicated to i.MX8M mini multicore MPU)
 - VisionCB-STM32MP1-STD (dedicated to STM32MP1 multicore MPU)
- Plug & Play solution for SoMLabs customers
- Integrated stereo audio channel
- Connection with carrier board using FPC30 cable A-A type

Pictures







Ordering info

SL-MIPI-LVDS-HDMI-CNV - FPC 30-pin flat cable (A-A) is included.


Operating ranges

Parameter	Value	Unit	Comment
Power Supply	3.3 & 5.0	V	Powered from carrier board
Current	0.1	A	Maximum peak value
Environment temperature	-40...+85	°C	-

Electrical parameters

Signal name	Parameter	Value			Units
		Min.	Typ.	Max.	
+5V	Supply Voltage	4.75	5.0	5.25	V
+3.3V	Supply Voltage	3.2	3.3	3.35	V
I _{5V}	Supply Current (5V)	40	80	100	mA
I _{3.3V}	Supply Current (3.3V)	1	2.2	8	mA
VIO _{I2C}	I2C Input Voltage	0	3.3	3.6	V
VIO _{RES/SPDIF}	RES/SPDIF Input Voltage	0	3.3	3.6	V
f _{I2C}	I2C Controller Speed	-	-	400	kHz
R _{INT}	Interrupt Output Pull-up Resistance	-	4.7	-	kΩ
R _{I2C}	I2C IOs Pull-up Resistance	-	4.7	-	kΩ


MIPI-DSI (input) Pinout



FPC30 connector pin	Function name	Description
1	GND	-
2	-	-
3	HPD	HPD line from HDMI (voltage translated to 3.3V)
4	+5V	Power supply (input)
5	+5V	Power supply (input)
6	+3.3V	Power supply (input)
7	+3.3V	Power supply (input)
8	GND	-
9	SPDIF-TX	SPDIF input from SBC
10	INT	Interrupt output (voltage translated to 3.3V)
11	RESET	Reset input (voltage translated to 3.3V)
12	GND	-
13	SDA	I2C SDA line (voltage translated to 3.3V)
14	SCL	I2C SCL line (voltage translated to 3.3V)
15	GND	-

16	D3n	MIPI-DSI lane 3 negative line
17	D3p	MIPI-DSI lane 3 positive line
18	GND	-
19	D2n	MIPI-DSI lane 2 negative line
20	D2p	MIPI-DSI lane 2 positive line
21	GND	-
22	D1n	MIPI-DSI lane 1 negative line
23	D1p	MIPI-DSI lane 1 positive line
24	GND	-
25	D0n	MIPI-DSI lane 0 negative line
26	D0p	MIPI-DSI lane 0 positive line
27	GND	-
28	CLKn	MIPI-DSI clock negative line
29	CLKp	MIPI-DSI clock positive line
30	GND	-


LVDS (output) Pinout



LVDS connector pin	Function name	Description
1	+5V	Power supply for external devices (max. 20 mA) Internally connected with pin 2
2	+5V	Power supply for external devices (max. 20 mA) Internally connected with pin 1
3	-	-
4	GND	-
5	GND	-
6	GND	-
7	D0n	LVDS D0n data line
8	D0p	LVDS D0p data line
9	D1n	LVDS D1n data line
10	D1p	LVDS D1p data line
11	D2n	LVDS D2n data line
12	D2p	LVDS D2p data line
13	GND	-


14	GND	-
15	CLKn	LVDS CLKn clock line
16	CLKp	LVDS CLKp clock line
17	D3n	LVDS D3n data line
18	D3p	LVDS D3p data line

HDMI (output) Pinout



HDMI connector built-in SL-MIPI-LVDS-HDMI-CNV converter has standard HDMI pinout.

Dimensions



**SoMLabs**

Lwowska 5
05-120 Legionowo
Poland
Tel. +48 22 767 36 20
Email: contact@somlabs.com
<http://somlabs.com>

Disclaimer: The information in this document is provided in connection with SoMLabs products. No license, express or implied, to any intellectual property right is granted by this document or in connection with the sale of SoMLabs products. SoMLabs makes no representations or warranties with respect to the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and products descriptions at any time without notice. SoMLabs does not make any commitment to update the information contained herein.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SoMLabs:](#)

[SL-MIPI-LVDS-HDMI-CNV](#) [SL-MIPI-LVDS-HDMI-CNV v.1.1](#)