




## Electrical Specifications

Parameter	Conditions & Remarks	Min	Max	Unit
Contact Resistance			100	milliohms
Insulation Resistance	Between insulated terminals	100		Megohms
Dielectric Strength	1 minute between adjacent switches		250	VAC
Nonswitching Rating			50 or 12	mA or VDC

## Mechanical and Environmental


Soldering	Maximum reflow temperature, 260°C for 5 seconds Maximum manual temperature, 350°C for 3 seconds
RoHS	Lead-Free. Fully compliant to RoHS Directive 2011/65/EU
Operating Force	160±50 gf 260±70 gf
Actuation Life	160 gf: 50,000 cycles 260 gf: 30,000 cycles
Actuator Strength	2 Kgf maximum
Travel	0.25±0.1 mm 0.15±0.1 mm (IP67)
Operating Temperature Range	-40°C to +85°C
Storage Temperature Range	-40°C to +85°C
Packaging	Standard tape and reel packaging

## Soldering Profile




### Mechanical Specifications


**Figure 1 – 222BMV, Surface Mount Gull Wing, Vertical Actuation, Not IP67**




**Figure 2 – 222BJV, Surface Mount J-Bend, Vertical Actuation, Not IP67**



**Figure 3 – 222BMV...6, Surface Mount Gull Wing, Vertical Actuation, IP67**



**Figure 4 – 222BJV...6, Surface Mount J Bend, Vertical Actuation, IP67**




### Packing: Tape and Reel

#### Surface Mount Gull Wing/J-Bend, Top Actuation


The packing specification:

Structure and materials:



No	PART NAME	MATERIAL
①	REEL	POLYSTYRENE
②	CARRIER TAPE	POLYSTYRENE
③	COVER TAPE	POLYESTER

1. More than 10 empty pockets should remain at each end of the carrier tape for each reel.
2. Shortage of less than 10 pcs a reel is acceptable but no more than 3 consecutive empty pockets are allowed.
3. Stripping strength of cover tape is between 10 gf to 70 gf and stripping angle should be within 165°~180°.
4. The product in the pocket of carrier tape should be placed in a specified correct position.
5. Tape and reel per EIA-481.
6. Dimensions:



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

[222BMVBAR](#) [222BMVABR](#) [222BMVBRR](#) [222BMVAAR](#) [222BJVABR](#) [222BJVBRR](#) [222BJVAAR](#) [222BJVBAR](#)