



Series 228B

6.0 x 6.0mm Illuminated Tactile Switch

- Surface mount gull-wing terminal and standard through hole configurations
- Compatible with IR reflow, and manual soldering
- Single color display during illumination
- Variety of LED color options
- Variety of cap shape, color, laser etching options



Ordering Information

Series	Terminal Type	Actuating Direction	Actuation Force	LED Color	LED Type	Cap Style	Cap Color	Laser Etching	Packaging																																																						
228B	M	V	A	R	F	AF	MS	A	R																																																						
<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>D</td><td>Standard through hole (white actuator)</td></tr><tr><td>M</td><td>Surface mount gull wing (black actuator)</td></tr></table>		Code	Spec.	D	Standard through hole (white actuator)	M	Surface mount gull wing (black actuator)	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>V</td><td>Vertical</td></tr></table>		Code	Spec.	V	Vertical	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>A</td><td>160 gf</td></tr></table>		Code	Spec.	A	160 gf	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>F</td><td>Flat</td></tr><tr><td>*Blank</td><td>Bulb</td></tr><tr><td colspan="2">*Blank is only available for no cap, through hole terminal and single color LED</td></tr></table>		Code	Spec.	F	Flat	*Blank	Bulb	*Blank is only available for no cap, through hole terminal and single color LED		<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>R</td><td>Red</td></tr><tr><td>Y</td><td>Yellow</td></tr><tr><td>G</td><td>Pure Green</td></tr><tr><td>B</td><td>Blue</td></tr><tr><td>W</td><td>White</td></tr><tr><td>A</td><td>Amber</td></tr><tr><td>RG</td><td>Red & Green</td></tr><tr><td>RB</td><td>Red & Blue</td></tr><tr><td>YG</td><td>Yellow & Green</td></tr><tr><td>RA</td><td>Red & Amber</td></tr><tr><td>AW</td><td>Amber & White</td></tr></table>		Code	Spec.	R	Red	Y	Yellow	G	Pure Green	B	Blue	W	White	A	Amber	RG	Red & Green	RB	Red & Blue	YG	Yellow & Green	RA	Red & Amber	AW	Amber & White	<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>R</td><td>Tape & reel packaging (only available for surface mount type)</td></tr><tr><td>Blank</td><td>Tray packaging (only available for standard through hole type)</td></tr></table>		Code	Spec.	R	Tape & reel packaging (only available for surface mount type)	Blank	Tray packaging (only available for standard through hole type)
Code	Spec.																																																														
D	Standard through hole (white actuator)																																																														
M	Surface mount gull wing (black actuator)																																																														
Code	Spec.																																																														
V	Vertical																																																														
Code	Spec.																																																														
A	160 gf																																																														
Code	Spec.																																																														
F	Flat																																																														
*Blank	Bulb																																																														
*Blank is only available for no cap, through hole terminal and single color LED																																																															
Code	Spec.																																																														
R	Red																																																														
Y	Yellow																																																														
G	Pure Green																																																														
B	Blue																																																														
W	White																																																														
A	Amber																																																														
RG	Red & Green																																																														
RB	Red & Blue																																																														
YG	Yellow & Green																																																														
RA	Red & Amber																																																														
AW	Amber & White																																																														
Code	Spec.																																																														
R	Tape & reel packaging (only available for surface mount type)																																																														
Blank	Tray packaging (only available for standard through hole type)																																																														

Blank – No Cap
See table on
page 2

Blank – No Etching
(only available on
Natural color caps)
See table on page.2

Blank – No Cap
See table on
pages 2 - 4

Note: Not all part
number combinations
are available. Please
review the notes on the
following pages.

Note: Caps supplied in bulk for
surface mount terminal
constructions and must be
installed after IR reflow

Cap Style

Code	Spec.
*AF	Square (10 x 10)
*BF	Square (12.5 x 12.5)
*CF	Round (Dia. 10)
*DF	Dome (Dia. 10)
*EF	Button (Dia. 14)
*F	Square with center dot (7.5 x 7.5)
G	Elliptical column (only available with arrow laser etching)
H	Bullet
J1	Hollow Cylinder, height 8.2mm
J2	Cylinder, height 10.3mm
K	Joystick button
L	Square (7.5 x 7.5)
M	Round (Dia.10)

- 1) AF, BF, CF, DF, EF are only available for through hole terminals
- 2) AF, BF, CF, F – etching not available for these cap styles. Cap supplied with a transparent center dot

Cap Color

Code	Cap Color
B	Black
V	Ivory
G	Gray

Only available for cap style of AF, BF, CF, F

Code	Cap Color
MS	Misty Silver
W	White
BB	Bright Black
R	Red
MB	Misty Black
A	Orange
N	Natural


Cap Etching

Code	Style
A	
B	
C	
D	OK
E	POWER

Cap Style Details


Style AF: Square in with Center Dot (10 x 10)

Ex. of Ivory
Frame with
Ivory Cap




Style CF: Round with Center Dot (Dia. 10mm)

Ex. of Black
Frame with Gray
Cap




Style BF: Square with Center Dot (12.5 x 12.5)

Ex. of Black
Frame with
Ivory Cap




Style DF: Dome (Dia. 10mm)

Ex. of Black
Frame with Ivory
Cap




Style EF: Button with Frame (Dia. 14)


Only available with POWER etching




Style J1: Hollow Cylinder, 8.2mm height



Style F: Square with Center Dot (7.5 x 7.5)




Style J2: Cylinder, 10.3mm height




Style G: Elliptical column

(Only available with natural color and no etching)




Style K: Joystick button

(Only available with natural color and no etching)



Style H: Bullet

(Only available with natural color and no etching)



Style L: Square (7.5x7.5)






Series 228B

Tactile Switch

Style M: Round (Dia.10)



Ex. of Misty
Silver Cap


Electrical Specifications

Parameter	Conditions & Remarks	Min	Max	Unit
Contact Resistance			100	milliohms
Insulation Resistance	Between insulated terminals	100		megohms
Dielectric Strength	1 minute between adjacent switches		250	VAC
Nonswitching Rating			50 or 12	mA or VDC

Mechanical and Environmental

Soldering	Maximum reflow temperature, 260°C for 5 seconds Maximum manual temperature, 350°C for 3 seconds
RoHS	Lead-Free. Fully compliant to RoHS Directive 2011/65/EU and 2015/863/EU
Operating Force	160±50 gf
Actuation Life	100,000 cycles
Actuator Strength	2 Kgf maximum
Travel	0.25 ±0.1mm
Packaging	Standard tape and reel packaging for surface mount gull wing terminal Tray packaging for standard through hole
Operating Temperature Range	-20°C to +70°C
Storage Temperature Range	-30°C to +80°C

Soldering Profile



LED Specifications

Color	Reversed Voltage	Forward Current	Recommended Operating Current	Forward Voltage	
				Nor	Max
Red	5 Vdc	20 mA	20 mA	1.7V	2.4V
Green	5 Vdc	20 mA	20 mA	1.9V	2.4V
Yellow	5 Vdc	20 mA	20 mA	1.9V	2.4V
Blue	5 Vdc	20 mA	20 mA	3.0V	3.6V
White	5 Vdc	20 mA	20 mA	3.0V	3.6V

Mechanical Specifications

Figure 1 – 228BDV, Standard Though Hole, Vertical Actuation




Figure 2 – 228BMV, Surface Mount Gull Wing, Vertical Actuation






Figure 3 – 228BDVA...HN, Standard Though Hole, Vertical Actuation, Bullet on Square, Natural Color Cap



**Figure 4 – 228BDVA...KN, Standard Though Hole, Vertical Actuation, Joystick
Button on Square, Natural Color Cap**




Packing: Tape and Reel

Surface Mount Gull Wing, Actuator Height 9.0mm

The packing specifications:

1. Structure and materials:





No	PART NAME	MATERIAL
①	REEL	POLYSTYRENE
②	CARRIER TAPE	POLYSTYRENE
③	COVER TAPE	POLYESTER

2. Packing quantity: 300 pcs/reel
3. More than 15 empty pockets should remain at each end of the carrier tape for each reel.
4. Shortage of less than 10 pcs a reel is acceptable but no more than 3 consecutive empty pockets are allowed.
5. Stripping strength of cover tape is between 10 gf to 130 gf and stripping angle should be within 165°~180°.
6. The product in the pocket of carrier tape should be placed in a specified correct position.
7. Tape and reel per EIA-481.
8. Dimensions:



Series 228B

Tactile Switch



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

[228BMVARR](#) [228BDVAWFEFRE](#) [228BMVAYFKNR](#) [228BMVAYFR](#) [228BDVAB](#) [228BDVABF](#) [228BDVAYGF](#)
[228BMVARGFR](#) [228BDVARBF](#) [228BMVAGFR](#) [228BDVAYF](#) [228BDVAR](#) [228BDVAWF](#) [228BMVARBFR](#)
[228BDVAA](#) [228BDVARF](#) [228BMVAWFR](#) [228BDVAY](#) [228BMVAYGFR](#) [228BDVARGF](#) [228BDVAW](#) [228BMVAAFR](#)
[228BDVAAF](#) [228BDVAG](#) [228BMVABFR](#) [228BDVAGF](#) [228BDVAWFDFBBA](#) [228BDVAWFNG](#) [228BDVAWFJ2AA](#)
[228BDVAWFLMSE](#) [228BDVAYFDFMBA](#) [228BDVAYFDFMSC](#) [228BDVAWFDFMBE](#) [228BDVAWFDFMSB](#)
[228BDVAWFDFWE](#) [228BDVAAWFLN](#) [228BDVAAWFMMSB](#) [228BDVABFDFWB](#) [228BDVABFJ1W](#)
[228BDVAGFDFBBD](#) [228BDVAGFDFWC](#) [228BDVAGFJ1BB](#) [228BDVARAFEFWE](#) [228BDVARAFJ1BB](#)
[228BDVARBFDFBBA](#) [228BDVARBFLMSE](#) [228BDVARFBFB](#) [228BDVAAWFJ1A](#) [228BDVAAWFMMSC](#)
[228BDVAAFWFG](#) [228BDVABFDFBBA](#) [228BDVABFGN](#) [228BDVABFLMSC](#) [228BDVAAFDFRD](#)
[228BDVAAFMMSD](#) [228BDVAAWFCFG](#) [228BDVAAWFDFBBD](#) [228BDVAAWFJ1BB](#) [228BDVAAWFJ1MS](#)
[228BDVAAWFJ2WB](#) [228BDVABFCFV](#) [228BDVABFDFMBD](#) [228BDVABFDFRA](#) [228BDVABFEFAE](#) [228BDVABFFB](#)
[228BDVABFLMSB](#) [228BDVAGFCFG](#) [228BDVAGFDFMBA](#) [228BDVAGFJ2RB](#) [228BDVAGFMMSB](#)
[228BDVARAFEFMBE](#) [228BDVARAFLN](#) [228BDVARBFEFBBE](#) [228BDVARBFGN](#) [228BDVARBFLMSC](#)
[228BDVARBFMN](#) [228BDVARFCFG](#) [228BDVARFEFWE](#) [228BDVARFJ1BB](#) [228BDVARGFDFMSE](#)
[228BDVARGFEFMBE](#) [228BDVARGFJ2MBB](#) [228BDVAWFAG](#) [228BDVARFJ1MS](#) [228BDVARFJ2MBB](#)
[228BDVARGFAFV](#) [228BDVARGFDFWA](#) [228BDVAYFDFRE](#) [228BDVARBFJ1W](#) [228BDVARBFMMSE](#)
[228BDVARFMMSA](#) [228BDVARGFDFBBE](#) [228BDVARGFDFRA](#) [228BDVARGFDFV](#) [228BDVARGFDFWB](#)
[228BDVARGFJ2BBA](#) [228BDVAWFDFBBB](#) [228BDVAWFDFMSA](#) [228BDVAWFJ1BB](#) [228BDVAWFJ2RB](#)