



Series 228D

6.8 x 5.0mm Illuminated Tactile Switch

- Surface mount gull-wing terminal and standard through hole configurations
- Compatible with IR reflow, and manual soldering
- Single color display during illumination
- Variety of LED color options
- Variety of cap styles, colors, and laser etching options



Ordering Information

Series	Terminal Type	Actuating Direction	Actuation Force	LED Color	LED Type	Cap Style	Cap Color	Laser Etching	Packaging						
228D	M	S1	A	R	F	A	MS	A	R						
<table><tr><th>Code</th><th>Spec.</th></tr><tr><td>D1</td><td>Standard through hole (black actuator), terminal length 1.5mm</td></tr><tr><td>M</td><td>Surface mount gull wing (black actuator)</td></tr></table>		Code	Spec.	D1	Standard through hole (black actuator), terminal length 1.5mm	M	Surface mount gull wing (black actuator)							Blank – No Etching (only available on Natural color caps) See table on page.2	
Code	Spec.														
D1	Standard through hole (black actuator), terminal length 1.5mm														
M	Surface mount gull wing (black actuator)														
								Blank – No Cap See table on page 2							
								Blank – No Cap See table on pages 2							
						</									

Note: Caps supplied in bulk for surface mount terminal constructions and must be installed after IR reflow soldering.

Cap Style


Code	Spec.
A	Cylinder on 3/4 circle

Cap Color

Code	Spec.
MS	Misty Silver
W	White
BB	Bright Black
R	Red
MB	Misty Black
A	Orange
N	Natural

Cap Style Details

Style A: Cylinder on 3/4 round



Cap Etching

Code	Style
A	
B	
C	


Electrical Specifications

Parameter	Conditions & Remarks	Min	Max	Unit
Contact Resistance			100	milliohms
Insulation Resistance	Between insulated terminals	100		megohms
Dielectric Strength	1 minute between adjacent switches		250	VAC
Nonswitching Rating			50 or 12	mA or VDC

Mechanical and Environmental

Soldering	Maximum reflow temperature, 260°C for 5 seconds Maximum manual temperature, 350°C for 3 seconds
RoHS	Lead-Free. Fully compliant to RoHS Directive 2011/65/EU and 2015/863/EU
Operating Force	220±50 gf
Actuation Life	100,000 cycles
Actuator Strength	2 Kgf maximum
Travel	0.25±0.1mm
Packaging	Standard tape and reel packaging for surface mount gull wing terminal Tray packaging for standard through hole
Operating Temperature Range	-25°C to +70°C
Storage Temperature Range	-30°C to +80°C

Soldering Profile



LED Specifications

Color	Reversed Voltage	Forward Current	Recommended Operating Current	Forward Voltage	
				Nor	Max
Red	5 Vdc	20 mA	20 mA	1.7V	2.4V
Green	5 Vdc	20 mA	20 mA	1.9V	2.4V
Yellow	5 Vdc	20 mA	20 mA	1.9V	2.4V
Blue	5 Vdc	20 mA	20 mA	3.0V	3.6V
White	5 Vdc	20 mA	20 mA	3.0V	3.6V

Mechanical Specifications

Figure 1 – 228DD1S1..., Standard Though Hole, Terminal Length 2.1mm, Side Actuation, Height: 3.5mm from cap center to PCB





Figure 2 – 228DMS, Surface Mount Gull Wing, Vertical Actuation




Packing: Tape and Reel

Surface Mount Gull Wing, Actuator Height 7.0mm


The packing specifications:

1. Structure and materials:



No	PART NAME	MATERIAL
①	REEL	POLYSTYRENE
②	CARRIER TAPE	POLYSTYRENE
③	COVER TAPE	POLYESTER

2. Packing quantity: 500 pcs/reel
3. More than 15 empty pockets should remain at each end of the carrier tape for each reel.
4. Shortage of less than 10 pcs a reel is acceptable but no more than 3 consecutive empty pockets are allowed.
5. Stripping strength of cover tape is between 10 gf to 130 gf and stripping angle should be within 165°~180°.
6. The product in the pocket of carrier tape should be placed in a specified correct position.
7. Tape and reel per EIA-481.
8. Dimensions:



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

[228DD1S1AAFAMSC](#) [228DD1S1AAFAAB](#) [228DD1S1AAWFAMBC](#) [228DD1S1ABFABBB](#) [228DD1S1ABFAMSC](#)
[228DD1S1AGFAAA](#) [228DD1S1AGFAAC](#) [228DD1S1AAF](#) [228DD1S1AAFAN](#) [228DD1S1AAFARB](#)
[228DD1S1ABFARC](#) [228DD1S1AAFAMBA](#) [228DD1S1AAWFAWC](#) [228DD1S1ABFAAA](#) [228DD1S1AAFARA](#)
[228DD1S1AAWFAMSA](#) [228DD1S1AAFAMSB](#) [228DD1S1AAWF](#) [228DD1S1AAFAAC](#) [228DD1S1AAFAWC](#)
[228DD1S1AAFAAA](#) [228DD1S1AAWFAWA](#) [228DD1S1ABFABBC](#) [228DD1S1ABFAMSB](#) [228DD1S1AAWFABBB](#)
[228DD1S1ABF](#) [228DD1S1ABFAAB](#) [228DD1S1ABFARB](#) [228DD1S1AAFAMSA](#) [228DD1S1ABFABBA](#)
[228DD1S1AGF](#) [228DD1S1ABFAN](#) [228DD1S1AGFAAB](#) [228DD1S1AAFARC](#) [228DD1S1AAFAWA](#)
[228DD1S1AAWFAMSB](#) [228DD1S1ARFAWB](#) [228DD1S1AYFARB](#) [228DD1S1AYGFAN](#) [228DMS1AGFAWCR](#)
[228DMS1ARAFABBAR](#) [228DMS1ARBFAAAR](#) [228DMS1ARGFABBCR](#) [228DMS1ARGFANR](#) [228DMS1ARGFR](#)
[228DMS1AWFR](#) [228DMS1AYGFAACR](#) [228DD1S1AGFAWA](#) [228DD1S1ARAFAMBB](#) [228DD1S1ARAFARB](#)
[228DD1S1ARGFAMBC](#) [228DD1S1AWFABBC](#) [228DD1S1AYFABBA](#) [228DD1S1AYGFARC](#) [228DD1S1AYGFAWA](#)
[228DMS1AAFAMSCR](#) [228DMS1AAFARAR](#) [228DMS1ABFAMBCR](#) [228DMS1ARBFAWAR](#) [228DMS1ARFAMSBR](#)
[228DMS1AWFABBAR](#) [228DMS1AYFAAAR](#) [228DMS1AYGFARAR](#) [228DMS1AYGFARCR](#) [228DMS1ARBFAFAMBAR](#)
[228DMS1ARFABBBR](#) [228DD1S1ARAF](#) [228DD1S1ARAFAC](#) [228DD1S1ARAFAWA](#) [228DD1S1ARBF](#)
[228DD1S1ARGFAMBA](#) [228DD1S1ARGFAMBB](#) [228DMS1AGFABBBR](#) [228DMS1ARAFAWAR](#) [228DMS1ARAFAWCR](#)
[228DMS1ARAFR](#) [228DMS1AYGFAWBR](#) [228DMS1ARGFARCR](#) [228DMS1AAFAMBAR](#) [228DMS1AAWFAMBAR](#)
[228DMS1AWFAMBBR](#) [228DMS1AWFAMSAR](#) [228DMS1AYGFAMSBR](#) [228DMS1AAWFANR](#) [228DMS1AGFARBR](#)
[228DMS1ARAFARCR](#) [228DMS1ARBFAFAMBAR](#) [228DMS1ARBFAWCR](#) [228DMS1ARFAMBBR](#) [228DMS1ARFAMSAR](#)
[228DMS1ARFARBR](#) [228DMS1AYGFABBBR](#) [228DMS1AYGFAMSCR](#) [228DMS1AYGFAYGR](#) [228DD1S1AGFAMBC](#)
[228DD1S1AGFAMSB](#) [228DD1S1ARBFAAC](#) [228DD1S1ARFARB](#) [228DD1S1AYFARC](#) [228DD1S1AYGFABBB](#)