




Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4101-000.
TUSONIX RoHS COMPLIANT PART NUMBER: 4101-000 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. RoHS COMPLIANT PART MARKED WITH GREEN DOT FOR IDENTIFICATION.

MIN. CAP. (pF)	WORKING VOLTAGE (WVdc)		CURRENT Idc.	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220			
	85°C	125°C				10 MHz	100 MHz	1 GHz	10 GHz
1750	250	125	10 A	10 G	500	5	35	50	50

X-2015 Rev-0	
REVISION RECORD	
0	Original Release C.O.
1	WAS SK 6644-080-S. LE 1-13-84
	DIM'S & TOL'S REV'D. RELEASED. L.E. 1-8-85
2	C.O.1653
	CURRENT UNIT "A" ADDED L.E. 8-20-85
3	2595
	RDN. TO COMP. FMT. S.M. 07-19-00
4	20000914-3-03
	DIM .145 TOL WAS ±.018. ADDED IR, DWV & CIRCUIT. S.M.11-05-04
5	20041105-1-01
	ADDED NOTES. S.M. 03-14-05
6	20050314-3-01
--TOLERANCES-- Unless Otherwise Specified	
DECIMAL ± .015 [0.38]	
ANGLES ± 	
TUSONIX TUCSON, ARIZONA	
Title EYELET STYLE EMI FILTER	
Drawn S.M. 07-19-00	
Scale 4 X	
Approved T.C. 07-19-00	
A	4101-000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4101-000LF](#)