

EM3526 Series Euro-Mag Terminal Blocks

Closed and Open Header (Mates with EM3516 Series); 7.62 Centers

SPECIFICATIONS

Rating: 16A, 300V

Center Spacing: 0.30" (7.62mm)

Housing Material: UL rated 94V0 Thermoplastic

Contact Material: Brass Tin-Plated

Operating Temperature: 105°C (221°F) max., -40°C (-40°F) min.

Recommended PCB Hole Diameters: 0.055" (1.40mm)

Construction: Mold-to-Length


Agency Information:  File E62622; CE Certified



Dimensions - mm (in)

Poles	Open L (mm)	Closed L (mm)
2	13.44	15.24
3	21.06	22.86
4	28.68	30.48
5	36.60	38.10
6	43.92	45.72
7	51.54	53.34
8	59.16	60.96
9	66.78	68.58
10	74.40	76.20
11	82.02	83.82
12	89.64	91.44

To convert to inches, divide by 25.4



Part Numbering System

Series

EM3526

of Poles

02 to 24

Orientation

H - horizontal
V - vertical

Side Base

O - open
C - closed

Mating Plug: EM3516 pg. 108

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

<u>EM352604VO</u>	<u>EM352610HC</u>	<u>EM352611VO</u>	<u>EM352612HC</u>	<u>EM352607VC</u>	<u>EM352608HO</u>	<u>EM352606HO</u>
<u>EM352608VO</u>	<u>EM352602VC</u>	<u>EM352604VC</u>	<u>EM352611HC</u>	<u>EM352609HO</u>	<u>EM352607VO</u>	<u>EM352607HO</u>
<u>EM352610VC</u>	<u>EM352605VC</u>	<u>EM352606HC</u>	<u>EM352609HC</u>	<u>EM352602VO</u>	<u>EM352611HO</u>	<u>EM352604HO</u>
<u>EM352605HO</u>	<u>EM352607HC</u>	<u>EM352603VO</u>	<u>EM352604HC</u>	<u>EM352612VO</u>	<u>EM352609VO</u>	<u>EM352602HC</u>
<u>EM352608HC</u>	<u>EM352610VO</u>	<u>EM352603VC</u>	<u>EM352611VC</u>	<u>EM352606VC</u>	<u>EM352612VC</u>	<u>EM352612HO</u>
<u>EM352609VC</u>	<u>EM352605HC</u>	<u>EM352608VC</u>	<u>EM352602HO</u>	<u>EM352606VO</u>	<u>EM352603HC</u>	<u>EM352603HO</u>
<u>EM352610HO</u>	<u>EM352605VO</u>					