



Model 520

Clipped Sine Wave TCXO/VC-TCXO

Features

- Ceramic Surface Mount Package
- Low Phase Jitter Performance
- Fundamental Crystal Design
- Frequency Range 13 – 52MHz *
- +1.8V, +2.5V, +2.8V, +3.0V and +3.3V Operation
- Voltage Control Option for Frequency Tuning [VC-TCXO]
- Tape and Reel Packaging, EIA-481

Applications

- GPS
- IoT and IIoT
- Wireless Connectivity
- Synchronous Ethernet
- Base Stations/Femto Cells
- Mobile Communication
- WiMax/Wi-Fi/WLAN
- Phase Locked Loop
- Test Equipment

Description

CTS Model 520 is a low cost, small size, high performance Temperature Compensated Crystal Oscillator [TCXO]. Employing analog IC technology that provides a clipped sine wave output, high order temperature compensation engine; coupled with a fundamental quartz crystal M520 has excellent stability and low jitter/phase noise performance.

Ordering Information

Model	Supply Voltage	Frequency Code [MHz]	Frequency Stability ²	Temperature Range	Frequency Tuning	Packaging																															
520	L	XXX	10	D	T	R																															
<table><tr><th>Code</th><th>Voltage</th></tr><tr><td>M</td><td>+1.8Vdc</td></tr><tr><td>N</td><td>+2.5Vdc</td></tr><tr><td>T</td><td>+2.8Vdc</td></tr><tr><td>R</td><td>+3.0Vdc</td></tr><tr><td>L</td><td>+3.3Vdc</td></tr></table>		Code	Voltage	M	+1.8Vdc	N	+2.5Vdc	T	+2.8Vdc	R	+3.0Vdc	L	+3.3Vdc	<table><tr><th>Code</th><th>Stability</th></tr><tr><td>05</td><td>±0.5ppm [GPS]</td></tr><tr><td>10</td><td>±1.0ppm</td></tr><tr><td>15</td><td>±1.5ppm</td></tr><tr><td>20</td><td>±2.0ppm</td></tr><tr><td>25</td><td>±2.5ppm</td></tr></table>		Code	Stability	05	±0.5ppm [GPS]	10	±1.0ppm	15	±1.5ppm	20	±2.0ppm	25	±2.5ppm	<table><tr><th>Code</th><th>Frequency Deviation</th></tr><tr><td>T</td><td>TCXO [No Voltage Control]</td></tr><tr><td>A</td><td>±5ppm Minimum ³</td></tr></table>		Code	Frequency Deviation	T	TCXO [No Voltage Control]	A	±5ppm Minimum ³		
Code	Voltage																																				
M	+1.8Vdc																																				
N	+2.5Vdc																																				
T	+2.8Vdc																																				
R	+3.0Vdc																																				
L	+3.3Vdc																																				
Code	Stability																																				
05	±0.5ppm [GPS]																																				
10	±1.0ppm																																				
15	±1.5ppm																																				
20	±2.0ppm																																				
25	±2.5ppm																																				
Code	Frequency Deviation																																				
T	TCXO [No Voltage Control]																																				
A	±5ppm Minimum ³																																				

Notes:

- 1] Refer to document 016-1454-0, Frequency Code Tables. 3-digits for frequencies <100MHz, 4-digits for frequencies 100MHz or greater.
- 2] Frequency vs. Temperature only.
- 3] See Electrical Characteristics for Voltage Control range per Supply Voltage selected.

Not all performance combinations and frequencies may be available.
Contact your local CTS Representative or CTS Customer Service for availability.

This product is specified for use only in standard commercial applications. Supplier disclaims all express and implied warranties and liability in connection with any use of this product in any non-commercial applications or in any application that may expose the product to conditions that are outside of the tolerances provided in its specification.



Electrical Specifications

Operating Conditions

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Maximum Supply Voltage	V_{CC}	-	-0.6	-	4.6	V
Maximum Control Voltage	V_C	-	-0.6	-	$V_{CC}+0.6$	V
Supply Voltage	V_{CC}	$\pm 5\%$	1.71	1.8	1.89	V
			2.38	2.5	2.63	
			2.66	2.8	2.94	
			2.85	3.0	3.15	
			3.14	3.3	3.47	
Supply Current	I_{CC}	13.00MHz - <26.00MHz	-	-	2.0	mA
		26.00MHz - 52.00MHz	-	-	2.5	
Output Load	$R_L//C_L$	-	10k Ohm//10pF			-
Operating Temperature	T_A		-20		+70	°C
			-30	+25	+85	
			-40		+85	
Storage Temperature	T_{STG}	-	-40	-	+85	°C

Frequency Stability

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Frequency Range	f_0	-		13 - 52		MHz
Frequency Stability						
Initial Calibration	$\Delta f/f_0$	Calibration @ +25°C, After 2 Reflows	-2.0	-	2.0	ppm
Temperature Only		Referenced to +25°C Reading		0.5, 1.0, 1.5, 2.0, 2.5		$\pm$ ppm
Voltage Coefficient	$\Delta f/f_{25}$	Supply Voltage, $\pm 5\%$	-0.2	-	0.2	ppm
Load Coefficient		Load, $\pm 10\%$	-0.2	-	0.2	ppm
Aging	$\Delta f/f_{25}$	First Year @ +25°C, nominal V_{CC} and V_C	-1.0	-	1.0	ppm
		10 Years @ +25°C, nominal V_{CC} and V_C	-10	-	10	

Output Parameters

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Output Type	-	DC Coupled		Clipped Sine		-
Output Voltage Levels	V_O	-	0.8	-	-	V_{P-P}
Start Up Time	T_S	Application of V_{CC}	-	-	2	ms
Phase Noise	-	See Typical Plots	-	-	-	-

Control Voltage


PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNIT
Control Voltage	V_C	1.8V	0.30	0.90	1.50	V
		2.5V, 2.8V, 3.0V, 3.3V	0.40	1.40	2.40	
Frequency Tuning [VCTCXO Only]	$\Delta f/f_0$	Specified V_C Range	± 5	-	-	ppm
Linearity	L	Best Straight Line Fit	-	± 5	± 10	%
Input Impedance	Z_{Vc}	-	500	-	-	kOhms
Transfer Function	-	-		Positive		-

Electrical Specifications

Test Circuit


Clipped Sine

* DC-Cut Capacitor: Add 1000pF capacitor between the TCXO output and input of load.



Output Waveform

Clipped Sine




Electrical Specifications


Performance Data

Phase Noise [typical]

26MHz, $V_{CC} = +3.3V$, $V_C = +1.4V$, $T_A = +25^\circ C$




52MHz, $V_{CC} = +3.3V$, $V_C = +1.4V$, $T_A = +25^\circ C$



Mechanical Specifications


Package Drawing



Marking Information

- xxx – Frequency Code.
3-digits for frequencies <100MHz
[See document 016-1454-0, Frequency Code Tables.]
- yyy – Crystal Lot Code or Date Code [Optional].
- – Pin 1 identifier.
- ** – Manufacturing Site Code.
- D – Date Code. See Table I for codes.

Recommended Pad Layout



Notes

- JEDEC termination code (e4). Barrier plating is nickel [Ni] with gold [Au] flash plate.
- Reflow conditions per JEDEC J-STD-020; +260°C maximum, 20 seconds.
- MSL = 1.

Pin Assignments

Pin	Symbol	Function
1	GND V _C	Ground [Note 1] Voltage Control [VC-TCXO]
2	GND	Circuit & Package
3	Output	RF Output [Note 2]
4	V _{CC}	Supply Voltage

Notes


- Connect to ground for TCXO, no frequency tuning. This pin can be left floating.
- DC-Cut Capacitor Required. Add 1000pF capacitor between TCXO output and input of load.

Table I - Date Code, Beginning year 2021


MONTH					JAN	FEB	MAR	APR	MAY	JUN	JUL	AUG	SEP	OCT	NOV	DEC
YEAR																
2021	2025	2029	2033	2037	A	B	C	D	E	F	G	H	J	K	L	M
2022	2026	2030	2034	2038	N	P	Q	R	S	T	U	V	W	X	Y	Z
2023	2027	2031	2035	2039	a	b	c	d	e	f	g	h	j	k	l	m
2024	2028	2032	2036	2040	n	p	q	r	s	t	u	v	w	x	y	z

Packaging - Tape and Reel

Tape Drawing



Reel Drawing



Notes

1. Device quantity is 1k pieces minimum and 3k pieces maximum per 180mm reel.
2. Complete CTS part number, frequency value and date code information must appear on reel and carton labels.



Addendum

Common Frequencies – MHz

FREQUENCY	ORDERING CODE	FREQUENCY	ORDERING CODE	FREQUENCY	ORDERING CODE	FREQUENCY	ORDERING CODE
14.400000	144	27.000000	270				
14.745600	147	30.720000	307				
16.000000	160	32.000000	320				
16.384000	163	38.400000	384				
18.432000	184	40.000000	400				
19.200000	192	44.000000	440				
20.000000	200	48.000000	480				
24.000000	240	50.000000	500				
25.000000	250	52.000000	520				
26.000000	260						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

520L14405CTR	520L14405DTR	520L14405ITR	520L14410CTR	520L14410DTR	520L14410ITR	520L14415CTR
520L14415DTR	520L14415ITR	520L14420CTR	520L14420DTR	520L14420ITR	520L14425CTR	520L14425DTR
520L14425ITR	520L14705CTR	520L14705DTR	520L14705ITR	520L14710CTR	520L14710DTR	520L14710ITR
520L14715CTR	520L14715DTR	520L14715ITR	520L14720CTR	520L14720DTR	520L14720ITR	520L14725CTR
520L14725DTR	520L14725ITR	520L16005CTR	520L16005DTR	520L16005ITR	520L16010CTR	520L16010DTR
520L16010ITR	520L16015CTR	520L16015DTR	520L16015ITR	520L16020CTR	520L16020DTR	520L16020ITR
520L16025CTR	520L16025DTR	520L16025ITR	520L16305CTR	520L16305DTR	520L16305ITR	520L16310CTR
520L16310DTR	520L16310ITR	520L16315CTR	520L16315DTR	520L16315ITR	520L16320CTR	520L16320DTR
520L16320ITR	520L16325CTR	520L16325DTR	520L16325ITR	520L18405CTR	520L18405DTR	520L18405ITR
520L18410CTR	520L18410DTR	520L18410ITR	520L18415CTR	520L18415DTR	520L18415ITR	520L18420CTR
520L18420DTR	520L18420ITR	520L18425CTR	520L18425DTR	520L18425ITR	520L19205CTR	520L19205DTR
520L19205ITR	520L19210CTR	520L19210DTR	520L19210ITR	520L19215CTR	520L19215DTR	520L19215ITR
520L19220CTR	520L19220DTR	520L19220ITR	520L19225CTR	520L19225DTR	520L19225ITR	520L20005CTR
520L20005DTR	520L20005ITR	520L20010CTR	520L20010DTR	520L20010ITR	520L20015CTR	520L20015DTR
520L20015ITR	520L20020CTR					