



2-port EtherCAT communication module for DA1 variable frequency drives

Part no. DX-NET-ETHERCAT-2  
169127

General specifications		
Product name		Eaton DX Communication module
Part no.		DX-NET-ETHERCAT-2
EAN		4015081656073
Product Length/Depth		51.8 millimetre
Product height		22.3 millimetre
Product width		50.1 millimetre
Product weight		0.03 kilogram
Compliances		CE
Product Tradename		DX
Product Type		Accessory
Product Sub Type		Communication module
Catalog Notes		2 x RJ45, 8 pole
General information		
Accessory/spare part type		Communication module
Product Category		Accessories
Used with		DA1
Climatic environmental conditions		
Ambient operating temperature - max		50 °C
Ambient operating temperature - min		-10 °C
Connection		
Connection type		Plug-in connection
Communication		
Protocol		EtherCAT
Design verification		
10.2.2 Corrosion resistance		Meets the product standard's requirements.
10.2.3.1 Verification of thermal stability of enclosures		Meets the product standard's requirements.
10.2.3.2 Verification of resistance of insulating materials to normal heat		Meets the product standard's requirements.
10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects		Meets the product standard's requirements.
10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of assemblies		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Meets the product standard's requirements.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9.2 Power-frequency electric strength		Is the panel builder's responsibility.
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function			The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
---------------------------	--	--	--

Technical data ETIM 9.0

Low-voltage industrial components (EG000017) / Accessories/spare parts for frequency controller (EC002025)			
Electric engineering, automation, process control engineering / Electrical drive / Static frequency converter / Static frequency converter (accessories) (ecl@ss13-27-02-31-92 [AFR303008])			
Type of accessory/spare part			Communication module
Accessory			Yes
Spare part			No

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[DX-NET-ETHERCAT-2](#)