

### Features

- Small Size
- Low Ripple
- High Rejection

### Description

Surface mount, silver (Ag) coated barium ceramic filter.

Weight: 1.0 grams typical.

Material: Filter is composed of a ceramic block plated with Ag.

Filter complies with RoHS standards.



### Electrical Specifications

|                               | Frequency<br>MHz | Typical<br>@ 25°C | Specification<br>@ 25°C | Spec over<br>-40°C to +85°C |
|-------------------------------|------------------|-------------------|-------------------------|-----------------------------|
| Passband lloss 1              | 2180 - 2200      | -0.5              | -0.70                   | -0.8                        |
| Passband Ripple 1             | 2180 - 2200      | 0.3               | 0.50                    | 0.6                         |
| Passband Return Loss @ Port 1 | 2180 - 2200      | -15.0             | -10.00                  | -10.0                       |
| Passband Return Loss @ Port 2 | 2180 - 2200      | -15.0             | -10.00                  | -10.0                       |
| Attenuation                   | 2000 - 2020      | -40.0             | -35.00                  | -35.0                       |
| Power into any port           |                  | 2 Watt max        |                         |                             |

Note: Supplier shall test each filter to the critical electrical specifications of the above table. Any subsequent audits may deviate from in value due to measurement repeatability among different test systems. Such deviations shall not exceed the following limits:


| Specification Allowance |        |
|-------------------------|--------|
| Insertion Loss          | 0.1 dB |
| Return Loss             | 1.0 dB |
| Stopbands               | 1.0 dB |

\*This product is covered by one or more of the following U.S. and foreign patents including: US 4,692,726;US 4,742,562; US 4,800,348;US 4,829,274;US 5,146,193;EP 0573597;DE 0573597;FR 0573597;JP 508149/92;KR 142171;US 5,162,760;US 5,218,329;US 5,250,916;US 5,327,109;US 5,488,335;CA 2114029;FR 9306297;GB 2273393;JP 3205337;KR 115113;CN 93106228.4;US 5,512,866;EP 0706719;DE 0706719;FR 0706719;GB 0706719;CN 95190359.4;US 5,602,518;US 5,721,520;US 5,745,018;EP 0910875;DE 0910875;DK 0910875;FR 0910875;GB 0910875;IE 0910875;JP 505182/98;KR 10-323013;US 5,994,978;US 6,462,629;CN 00810420.4;US 6,559,735;US 6,650,202;US 6,834,429.Other US and foreign patents pending.

\*CTS Corporation 2006 reserves all copyrights in the layout, design and configuration of the patterns on this product.\*

### Mechanical Drawing



Rev 0 – Origin Date: November 12, 2008 – Revision Date: November 12, 2008



| Dim | Nominal (mm) | Tolerance (mm)<br>+/- or max |
|-----|--------------|------------------------------|
| A   | 10.00        | max                          |
| B   | 4.20         | max                          |
| C   | 0.91         | 0.13                         |
| D   | 0.91         | 0.13                         |
| E   | 0.86         | 0.13                         |
| F   | 1.20         | 0.13                         |
| G   | 7.50         | 0.13                         |
| H   | 4.00         | max                          |
| I   | 0.91         | 0.13                         |
| J   | 5.22         | max                          |


### Electrical response

### PCB Layout




### Packaging and Marking

| DIMENSION     | UNITS | SPECIFICATION |
|---------------|-------|---------------|
| REEL DIAMETER | mm    | 330           |
| REEL WEIGHT   | kg    | 1.6           |
| REEL QUANTITY | ea.   | 1000          |



CTS  
628  
YWW



| Wo        | Ao          | Bo           | Ko          | Po           |
|-----------|-------------|--------------|-------------|--------------|
| Inches/mm | Inches/mm   | Inches/mm    | Inches/mm   | Inches/mm    |
| 0.945"/24 | 0.217"/5.50 | 0.406"/10.30 | 0.169"/4.30 | 0.472"/12.00 |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[CTS:](#)

[CER0628A](#)