

Features

- High Rejection
- Low ripple

Description

Surface mount, silver (Ag) coated barium ceramic filter.

Weight: 2.5 grams typical

Material: Filter is composed of a ceramic block plated with Ag.

Filter complies with RoHS standards.



Electrical Specifications

Parameter	Frequency MHz	Typical @ 25°C	Specification @ 25°C	Spec over -40°C to +85°C
Response				
Passband Iloss	2412 - 2462	-2.60	-3.10	-3.40
Passband Ripple	2412 - 2462	0.70	0.90	1.00
Passband Return Loss @ Port 1	2412 - 2462	-14.50	-12.00	-12.00
Passband Return Loss @ Port 2	2412 - 2462	-14.50	-12.00	-12.00
Attenuation	0.1 - 2325	-55.00	-45.00	-45.00
	2387	-29.00	-25.00	-25.00
	2487	-27.00	-25.00	-25.00
	2575 - 4000	-46.00	-40.00	-40.00
Power into any port		1 Watt max		


Note: Supplier shall test each filter to the critical electrical specifications of the above table. Any subsequent audits may deviate from in value due to measurement repeatability among different test systems. Such deviations shall not exceed the following limits:

Specification Allowance	
Insertion Loss	0.1 dB
Return Loss	1.0 dB
Stopbands	1.0 dB

*This product is covered by one or more of the following U.S. and foreign patents including: US 4,692,726;US 4,742,562; US 4,800,348;US 4,829,274;US 5,146,193;EP 0573597;DE 0573597;FR 0573597;JP 508149/92;KR 142171;US 5,162,760;US 5,218,329;US 5,250,916;US 5,327,109;US 5,488,335;CA 2114029;FR 9306297;GB 2273393;JP 3205337;KR 115113;CN 93106228.4;US 5,512,866;EP 0706719;DE 0706719;FR 0706719;GB 0706719;CN 95190359.4;US 5,602,518;US 5,721,520;US 5,745,018;EP 0910875;DE 0910875;DK 0910875;FR 0910875;GB 0910875;IE 0910875;JP 505182/98;KR 10-323013;US 5,994,978;US 6,462,629;CN 00810420.4;US 6,559,735;US 6,650,202;US 6,834,429. Other US and foreign patents pending.


CTS Corporation 2006 reserves all copyrights in the layout, design and configuration of the patterns on this product.

Mechanical Drawing




Dim	Nominal (mm)	Tolerance (mm) +/- or max
A		
B	26.3	max
C		
D	4.01	0.25
E	18.27	0.13
F		
G	1.02	0.13
H	0.79	0.13
I	0.79	0.13
J	1.02	0.13
K	5.0	max
L	4.05	max
M	4.8	max
N	0.76	0.13

Electrical response




PCB Layout





Packaging and Marking

DIMENSION	UNITS	SPECIFICATION
REEL DIAMETER	mm	330
REEL WEIGHT	kg	2.7
REEL QUANTITY	ea.	500



Product Marking



MODEL NO.	Wo	Ao	Bo	Ko	Po
	44.0/(1.732)	5.30/(0.209)	26.80/(1.055)	5.00/(0.197)	8.0/(0.315)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CTS:

CER0368A