



A	B	C	D	E	F	G	H
---	---	---	---	---	---	---	---



	5	4
--	---	---

H
G
F
E
D
C
B
A



- NOTES**
1. OPERATING TEMPERATURE RANGE -55°C TO +125°C.
  2. GOLD PLATED CASE AND LEAD.
  3. EPOXY SEALED ON THE OPPOSITE END FROM THE GLASS SEAL.
  4. PROPER INSTALLATION REQUIRES FIRM STEADY PRESSURE UNTIL FLANGE IS FULLY SEATED.
  5. RECOMMENDED MOUNTING HOLE: .085±.001 [2.18±0.01]
  6. END OF LEAD INDICATED TO BE FREE OF BURRS.
  7. TUSONIX NON-RoHS COMPLIANT PART NUMBER: 4310-013.  
TUSONIX RoHS COMPLIANT PART NUMBER: 4310-013LF.  
CUSTOMER MUST SPECIFY NON-RoHS OR RoHS PART NUMBER WHEN ORDERING.
  8. COLOR CODE: BLACK/BLACK ON WHITE BACKGROUND. RoHS COMPLIANT PART MARKED WITH ADDITIONAL GREEN DOT FOR IDENTIFICATION.



B	Cx (pF)		DC WORKING VOLTAGE		I <sub>DC</sub>	I.R. MIN @ 100 VDC	DWV	DIMENSIONS: ENGLISH UNITS - INCHES METRIC UNITS - [ mm ]	 A Subsidiary of CTS Electronic Components TUCSON, ARIZONA	Title <b>MINIATURE PRESS-IN EMI FILTER</b>		
	1 TYP. 3 MAX.		85°C 150	125°C 100	1A	10 G Ω	250 VDC			Dwn <b>R.C. 12-01-15</b> Kcd <b>R.C. 12-01-15</b>		
	TYPICAL NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220								ORIENTATION 	<b>--TOLERANCES-- Unless Otherwise Specified</b>		
	10 MHz		100 MHz		1 GHz		10 GHz					
-----		-----		-----		-----						
A	REVISION RECORD										<b>2 Place Decimal ± .01</b>	
	REV	DATE	CHG BY	CHANGE	REV	DATE	CHG BY	CHANGE	<b>3 Place Decimal ± .005</b>			
	A	12-01-15	R.C.	ORIGINAL RELEASE								
	B	09-20-16	R.C.	MODIFY DOT LOCATION, NOTE 5 HOLE							<b>Angles ± 5 °</b>	
				DIM. ADDED EPOXY FILL, NOTE					<b>A</b> <b>4310-013</b>			
			</									

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4310-013LF](#)