





MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC []

This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.


Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.



.090 ±.005
 [2.29 ± 0.12]
 SQUARE



ELECTRODE
 TERMINATION
 SEE NOTE 5



**SUGGESTED
 MOUNTING PATTERN**

1. INDUCTANCE TO BE 0.1 μ H MINIMUM.
2. PACKAGE: BLISTER TAPE TO IEC-60286-3 TYPE II AND EIA-481-A.
 FOR 2,000 PIECE REEL ADD "M" TO THE PART NUMBER
 FOR 7,000 PIECE REEL ADD "T" TO THE PART NUMBER
3. TUSONIX NON-RoHS PART NUMBER:
 4700-008 M OR 4700-008 T.
 TUSONIX RoHS COMPLIANT PART NUMBER:
 4700-008 M LF OR 4700-008 T LF.
 CUSTOMER MUST SPECIFY STANDARD OR RoHS
 PART NUMBER WHEN ORDERING.
4. PART MARKING: STANDARD PART: NO MARKING.
 RoHS PART: LABELED ON PACKAGING ONLY.
5. ELECTRODE TERMINATION: STANDARD 60/40
 SOLDER; RoHS COMPLIANT - MATTE TIN.

CAP.		TOLERANCE	WVDC		TEST VOLTAGE	I.R.MIN. @ 100 (VDC.)	IDC	TYPICAL NO LOAD INSERTION LOSS dB AT 25°C PER MIL-STD-220		
			85°C	125°C				10 MHZ	100 MHZ	1 GHZ
4000 pF		+80% / -20%	100	50	300 VDC	10 G Ω	10 A	13	52	70

REVISION RECORD Original Release C.O. REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 02-13-03 20030213-1-05 REVISED DRAWING. S.M. 06-20-03 20030619-2-04 ADDED NOTES 3-5. S.M. 06-13-05 20050607-5-03 ADDED PROPERTY NOTE. S.M. 03-12-07 20070301-1-05 WVDC 125°C AND 50 ADDED L.E. 11-20-09 ECO-1055 NOTES 2,3, REVISED L.E.10-08-12 ECO-3124	0	12	13	14	15	B	C	--TOLERANCES-- Unless Otherwise Specified DECIMAL ± .005 [0.13] ANGLES ±  TUSONIX TUCSON, ARIZONA		Title SURFACE MOUNT SQUARE STYLE PI FILTER		
									Drawn FG 9-9-94		Scale 7 X	
									Approved NV 9-9-94		A 4700-008	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4700-008MLF](#)