

# Series 287 24mm Rotary Potentiometer


Ceramic Printed ElementHigh Rated Power: 2 watts

Rotational Torque: 600 ± 200 gf-cm
 Rotational Life: 100,000 cycles
 Ingression Protection Rating: IP50
 Rugged Metal Shaft and Bushing

Solder Lug, PC Mount and Flexible Lead Options



## **Ordering Information**



## **Electrical Specifications**

Parameter	Conditions & Remarks	Min	Max	Unit
Resistance Range	Linear	500	1Meg	Ω
Dielectric Strength	1 minute		750	VAC
Power Rating	@ 70°C		2.0	watt
Operating Voltage			500	VDC
Insulation Resistance	250 VDC	100		MΩ
Resistance Tolerance	Standard: ± 20%			
	Special: ± 10%			
Independent Linearity	± 5%			
Effective Electrical Angle	274°			

#### Mechanical and Environmental

Parameter	Conditions & Remarks	Min	Max	Unit	
Operating Temperature Range		-40	+120	°C	
Rotational Life	Element Wear	100,000		cycles	
Mechanical Angle			312	٥	
Stop Strength	9 kg-cm (7.8 in-lb)				
Rotational Torque	400 to 800 gf-cm (5.5 to 11.1 oz-in)				
Push-Pull Strength of Shaft	13.6 kg for 10 seconds				
Ingression Protection	IP50, optional IP67				
Mounting Torque	28.8 kg-cm (25 in-lb) max.				
Weight	22g typical (weights vary based on shaft and bushing sizes)				
Soldering Condition	Maximum temperature of 260°C for 5 seconds				
Marking	CTS logo, part number and date code				
Packaging	Standard cardboard box packaging		·		


All testing is performed at room ambient conditions except as noted. Users should verify device actual performance in their specific applications.

This product is compliant to RoHS3 Directive 2015/863 Amendments of Annex II on 31 March 2015, and REACH SVHC Directive EC 1907/2006 Amendments of Annex XIV & Annex XVII on 15 January 2018.

Custom and value-added options available on request. Please contact your sales representative for additional information.

## **Electrical and Mechanical Specifications**


#### Shaft Diameter and Trim Options




R-Round F-Flatted S-Slotted

## **Electrical and Mechanical Specifications**

#### Series 287 Metal Shaft, Bushing Mount, Printed Circuit "X" Type Terminals





#### Series 287 Metal Shaft, Bushing Mount, Wire Lead "C" Type Terminals




## **Electrical and Mechanical Specifications**


Series 287 Metal Shaft, Bushing Mount, Solder Lug "T" Type Terminals






#### Series 287 Metal Shaft, Split Lock Bushing Mount, Solder Lug "T" Type Terminals







## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### CTS:

```
287T364R103A11 287T328S103A11 287T328S104A11 287T328S105A11 287T328S202A11 287T328S102A11 287T364R202A11 287T520S504A11 287T328S504A11 287T364R102A11 287T364R104A11 287T364R105A21 287T520S103A11 287T520S202A11 287T520S252A11 287T520S501A11 287T520S502A11 287T520S503A11 287T364R503A11 287T364R504A11 287T364R504A21 287T328S203A11 287T328S203A11 287T328S253A11 287T328S253A11 287T328S253A11 287T328S253A11 287T328S253A11 287T328S253A11 287T328S254A11 287T328S501A11 287T364R501A11 287T364R502A11
```