

Locking Storage Cart for Mobile Devices and AV Equipment - Black

MODEL NUMBER: CSCSTORAGE1



Locking steel cabinet on rolling casters offers secure portable storage for tablets, cables and other mobile devices.

Features

Secure Storage Cart Provides Ample Space for Laptops, Tablets and Cables

Constructed from heavy-duty steel with a black powder-coated finish, this SmartRack® mobile cart provides safe, secure storage for your laptops, tablets and other valuable electronics. The front and back doors lock with the included keys to help prevent theft, damage and tampering. For extra security, the doors can be fastened with user-supplied padlocks. Flow-through vents on the doors and side panels help protect the devices against overheating, and the specially coated shelves help prevent device scratches and scuffs.

Moving Your Devices from Room to Room Is Easy

Large swivel casters with non-marking wheels improve the ride over uneven surfaces, including carpeting and thresholds, and lock to help prevent unwanted movement. The reversible wide-grip handle makes the cart easy to control. Corner safety bumpers protect walls and doorways from scratches. The compact cart takes up about the same amount of physical space, or even less, as a typical A/V cart.

Laminated Wood-Grain Top Doubles as a Convenient Workstation

The laminated top acts as a smooth writing surface and holds a projector, monitor or other peripherals. Those external devices plug into two NEMA 5-15R outlets. You can also mount a flat-screen monitor or television using CSC36DM Display Mount Adapter Kit (sold separately). The storage cart is powered by a 10-foot cord and NEMA 5-15P plug that connects to a compatible AC outlet.

Comes Ready for Immediate Use Right from the Box

The CSCSTORAGE1 AC Secure Storage Cart ships fully assembled for instant deployment in your school, office, retail establishment, government facility or other setting that relies on the daily use of mobile devices.

Highlights

- Steel enclosure locks with included keys to discourage theft, damage and tampering
- External NEMA 5-15R outlets provide power to devices, such as a laptop or projector
- Laminated wood-grain top serves as a smooth surface for writing or holding peripherals
- Vented side panels and doors allow flow-through ventilation to prevent overheating
- 10 ft. cord with NEMA 5-15P plug allows great flexibility in reaching AC outlets

Applications

- Secure devices in medical facilities, schools, businesses and government organizations that rely on the daily use of mobile devices
- Easily and safely transport mobile devices from room to room with a smooth, controlled ride
- Use the laminate top as a workstation or a sturdy platform for A/V equipment

Package Includes

- CSCSTORAGE1 AC Secure Storage Cart
- Reversible handle
- (2) Protective bumpers
- (12) Hex screws
- Hex key
- (2) Keys
- Owner's manual

Specifications

OVERVIEW

UPC Code

037332257116



Powering Business Worldwide

TRIPP LITE
SERIES

Product Type	Storage Cart
Charging Form Factor	Mobile Cart
Charger Functions	Charge; Secure
Device Compatibility	Amazon Kindle; Chromebook; Computer; DVR; Headphones; Laptop; Monitor/HDTV; Network Switch; Patch Panel; Phone; Projector; Server; Tablet; UPS; Watch
Device Slots	3
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Connection Type	5-15P - NEMA 5-15P RIGHT ANGLE
Voltage Compatibility (VAC)	120
Input Frequency	60
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Frequency Compatibility	60 Hz
PHYSICAL	
Color	Black
Material of Construction	Steel/Wood
Rack Height	0U
Rack Depth	Mid; Shallow
Charging Station Form Factor	Mobile Cart
Maximum Device Depth (cm)	58.17
Maximum Device Depth (in.)	22.90
Maximum Device Depth (mm)	582
Shipping Dimensions (hwd / in.)	46.85 x 26.77 x 29.13
Shipping Dimensions (hwd / cm)	119.00 x 68.00 x 73.99
Shipping Weight (lbs.)	165.00
Shipping Weight (kg)	74.84
Slot Dimensions (hwd / in.)	11.0 x 23.36 x 22.90
Slot Dimensions (hwd / mm)	280.00 x 593.00 x 582.00
Unit Dimensions (hwd / in.)	43.050 x 26.040 x 28.840
Unit Dimensions (hwd / cm)	109.35 x 66.14 x 73.25
Unit Weight (lbs.)	129.520
Unit Weight (kg)	58.75



Powering Business Worldwide

TRIPP LITE
SERIES

Weight Capacity - Stationary (kg)	45
Weight Capacity - Stationary (lbs.)	100
Number of Shelves	3
FEATURES & SPECIFICATIONS	
Grounding Details	No
Antimicrobial	No
Built-In Circuit Breaker	No
Cord Management	Yes
Overcurrent Protection	No
EMI/RFI Line Noise Protection	No
Flow-Through Ventilation	No
IP68 Rated	No
IP20 Rated	No
UV Sterilization	No
Built-in Cable Management	No
Extra Wide	No
Locking	No
Lock Type	Key
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico); UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty
CATEGORY PAGE FILTERS (Y/N ONLY)	
External Receptacle	No

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[CSCSTORAGE1](#)