





This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

# **MARKETING SALES DRAWING** **DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING** **DIMENSIONS IN METRIC - [ ]**

**Electrical Testing**  
**per Tusonix standard**  
**test plans and Mil-Std-202**  
**Test Methods.**



NOTE:  
LEAD ORIENTATION  
TO HEX NUT REQ'D.



## **NOTES:**

1. TUSONIX STANDARD PART NUMBER: 2432-032-X5U0-402M.  
TUSONIX RoHS COMPLIANT PART NUMBER: 2432-032-X5U0-402M LF.  
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. MATERIALS: SILVER PLATED BUSHING, LEAD, AND MOUNTING HARDWARE.
3. PART MARKING: 3 DOT COLOR CODE; STANDARD PART: COLORS PER VARIATION.  
RoHS PART: 3 DOT COLOR CODE PER VARIATION PLUS ADDITIONAL GREEN INK DOT OPPOSITE ON TOP OF HEX.
4. SUPPLIED WITH HEX NUT AND LOCK WASHER.
5. MAXIMUM RECOMMENDED MOUNTING TORQUE, 9.0 lb-in [1.02 Nm]

## **SPECIFICATIONS**

TUSONIX PART NO.	2432-032-X5U0-402M
Capacitance:	4000 pF
Tolerance:	± 20 %
Temp. Coefficient:	X5U
Operating Temp.:	-55°C TO 85°C
Working Voltage:	2000 VDC
To Tusonix Spec Unless Stated Otherwise	

REVISION RECORD	0	1	2	3
Original Release	5871			
REV'D. F.G. 04-30-91				
5901				
RDN TO COMP FMT.				
S.M. 07-18-00				
20000717-5-02				
ADDED NOTES & GREEN DOT.				
S.M. 05-02-06				
20060501-1-03				

--TOLERANCES-- Unless Otherwise Specified	Title <b>HIGH VOLTAGE FEED - THRU CAPACITOR</b>	
DECIMAL ± .015 [0.38]	Drawn S.M. 07-13-00	Scale 2 X
ANGLES ±	Approved T.C. 07-13-00	
<b>TUSONIX</b> TUCSON, ARIZONA	<b>A</b>	<b>2432-032-X5U0-402M</b>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2432-032-X5U0-402MLF](#)