

EM3108 Series**EuroMag Terminal Blocks**

Pluggable Block; Front Entry (Mates with EM2575 Series); 5.08 Centers

SPECIFICATIONS

Rating: 16A, 300V

Center Spacing: 0.20" (5.08mm)

Wire Range: #12-24 AWG

Housing Material: UL rated 94V0 Thermoplastic

Contact Material: Brass Tin-Plated

Cage Material: Brass, Nickel-Plated

Screw Size: M2.6 Zinc-Plated Steel

Operating Temperature: 105°C (221°F) max., -40°C (-40°F) min.


Torque Rating: 4.5 lb-in.

Construction: Mold-to-Length

Agency Information:  US File E62622; CE Certified



EM310808

Dimensions - mm

Poles	L (mm)	Poles	L (mm)
2	10.16	14	71.12
3	15.24	15	76.20
4	20.32	16	81.28
5	25.40	17	86.36
6	30.48	18	91.44
7	35.45	19	96.52
8	40.64	20	101.60
9	45.72	21	106.68
10	50.80	22	111.76
11	55.88	23	116.84
12	60.96	24	121.92
13	66.04		

To convert to inches, divide by 25.4

Part Numbering System

Series

of Poles

EM3108

02

02 to 24

Mating Header: EM2575 pg. 92

Terminal Blocks:
Single Row

EuroMag Series
Plug & Header

Edge Connectors,
One-Sided Boards

Compliance
References

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[EM310809](#) [EM310817](#) [EM310807](#) [EM310814](#) [EM310823](#) [EM310819](#) [EM310803](#) [EM310811](#) [EM310821](#)
[EM310822](#) [EM310820](#) [EM310824](#) [EM310802](#) [EM310806](#) [EM310808](#) [EM310818](#) [EM310813](#) [EM310816](#)
[EM310805](#) [EM310812](#) [EM310804](#) [EM310810](#) [EM310815](#)