

HCV1605

High current power inductors



Product features

- Flat-wire construction
- Low DCR, high efficiency
- Secure 3 terminal mounting
- 15.5 mm x 14 mm footprint surface mount package in a 4.98 mm height
- Ferrite core material
- Moisture Sensitivity Level: 1

Applications

- Compatible with Picor® Cool-Power® ZVS Buck and Buck-Boost Regulator Families

Environmental data

- Storage temperature range (Component): -55 °C to +125 °C
- Operating temperature range: -55 °C to +125 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant
- Halogen free, lead free, RoHS compliant



Picor® and Cool-Power® are trademarks of Vicor Corporation.


Product specifications

Part Number ⁷	OCL ¹ (μ H)	FLL ² (μ H) minimum	I _{rms} ³ (A)	I _{sat} ¹⁴ (A)	I _{sat} ²⁵ (A)	I _{sat} ³⁶ (A)	DCR (m Ω) maximum @ +20 °C
HCV1605R1-R375-R	0.375 \pm 6%	0.346	20	60	53	50	1.98
HCV1605R1-R500-R	0.500 \pm 10%	0.441	20	45	40	37	1.98


1. Open Circuit Inductance (OCL) Test Parameters: 100 kHz, 0.1 Vrms, 0.0 Adc, +25 °C
2. Full Load Inductance (FLL) Test Parameters: 100 kHz, 0.1 Vrms, I_{sat}¹, +25 °C
3. I_{rms}³: DC current for an approximate temperature rise of 40 °C without core loss. Derating is necessary for AC currents. PCB layout, trace thickness and width, air-flow, and proximity of other heat generating components will affect the temperature rise. It is recommended that the temperature of the part not exceed +125 °C under worst case operating conditions verified in the end application.

4. I_{sat}¹: Peak current for approximately 2% rolloff @ +25 °C
5. I_{sat}²: Peak current for approximately 20% rolloff @ +100 °C
6. I_{sat}³: Peak current for approximately 20% rolloff @ +125 °C
7. Part Number Definition: HCV1605Rx-Rxxx-R
HCV1605= Product code and size
Rx= Version indicator
Rxxx= Inductance value in μ H, R= decimal point,
If no R is present last character equals number of zeros
-R suffix = RoHS compliant


Dimensions (mm)



Recommended Pad Layout




Schematic




Part marking: HCV1605Rx-Rxxx, Rx= version indicator, Rxxx= inductance value in μ H, R= decimal point, if no R is present last character equals number of zeros
xxxx=lot code
All soldering surface to be coplanar within 0.1 millimeters
Tolerances are \pm 0.15 millimeters unless stated otherwise
Pad layout tolerances are \pm 0.1 millimeters unless stated otherwise
Pin 3 is for mounting stability. No connection.
Terminal: Pins (1,2) - Copper, Pin (3) - Bronze
Terminal finish: Pins (1,2) Tin-silver-copper, Pin (3) Copper-nickel-gold
Do not route traces or vias underneath the inductor

Packaging information (mm)



Supplied in tape and reel packaging , 500 parts per 13" diameter reel



Temperature rise vs. total loss



Inductance characteristics



Solder reflow profile




Table 1 - Standard SnPb Solder (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5mm)	235 °C	220 °C
≥2.5mm	220 °C	220 °C

Table 2 - Lead (Pb) Free Solder (T_C)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6mm	260 °C	260 °C	260 °C
1.6 – 2.5mm	260 °C	250 °C	245 °C
>2.5mm	250 °C	245 °C	245 °C

Reference JDEC J-STD-020

Profile Feature	Standard SnPb Solder	Lead (Pb) Free Solder
Preheat and Soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 Seconds	60-120 Seconds
Average ramp up rate T_{smax} to T_p	3°C/ Second Max.	3 °C/ Second Max.
Liquidous temperature (T_L)	183 °C	217 °C
Time at liquidous (t_L)	60-150 Seconds	60-150 Seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)** within 5 °C of the specified classification temperature (T_C)	20 Seconds**	30 Seconds**
Average ramp-down rate (T_p to T_{smax})	6 °C/ Second Max.	6 °C/ Second Max.
Time 25 °C to Peak Temperature	6 Minutes Max.	8 Minutes Max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2018 Eaton
All Rights Reserved
Printed in USA
Publication No. 10828 BU-MC18060
August 2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Eaton:

[HCV1605R1-R500-R](#)