




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



SPECIFICATIONS

CAP. VALUE:	1000 pF
CAP. TOL.:	+100, -0%
TEMP. CHAR.:	X5U
RATING:	500 VDC @ +85°C 250 VDC @ +125°C
OPERATING RANGE:	-55°C TO +125°C
CURRENT (A)	20
I.R. MIN. @ 100 VDC:	10 GΩ
DWV:	1250 VDC
MARKING: CAP CODE	102

NOTES:

1. TUSONIX STANDARD PART NUMBER: 2451-001-X5U0-102P.
TUSONIX RoHS COMPLIANT PART NUMBER:
2451-001-X5U0-102P LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART
NUMBER WHEN ORDERING.
2. LEAD FINISH: SILVER.
3. SHELL FINISH: SILVER.
4. PART MARKING: 3 DIGIT CAPACITANCE CODE STAMPED ON
SIDE OF SHELL. STANDARD PART: BLACK INK. RoHS PART:
DARK GREEN INK.

X-2015 Rev-0

REVISION RECORD

Original Release C.O. 20050907-8-02	0
Reissue: Corrected Dwg No. EC 2-03-06	1
20050907-8-02	

--TOLERANCES--
Unless Otherwise
Specified

DECIMAL $\pm$ NOTED

ANGLES $\pm$

TUSONIX
TUCSON, ARIZONA

Title

**DISCOIDAL
STAND-OFF
CAPACITOR**

Drawn

L.E. 02-02-06

Scale

4 X

Approved

B.Mc. 02-02-06

A

2451-001-X5U0-102P

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[2451-001-X5U0-102PLF](#)