




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.



MARKETING SALES DRAWING **DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING** **DIMENSIONS IN METRIC - []**



Electrical Testing
per Tusonix standard
test plans and Mil-Std-202
Test Methods.




MOUNTING HARDWARE



NOTES:

1. TUSONIX STANDARD PART NUMBER: 4402-060.
TUSONIX RoHS COMPLIANT PART NUMBER: 4402-060 LF.
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD, BUSHING AND MOUNTING HARDWARE: SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS.
STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. OPERATING TEMPERATURE RANGE: -55°C TO +125°C.
5. MAX. RECOMMENDED SOLDERING TEMPERATURE: 260°C.
6. SUPPLIED WITH HEX NUT AND INTERNAL TOOTH LOCK WASHER.
7. MAX. RECOMMENDED MOUNTING TORQUE: 2.0 Lb.-IN.

MIN. CAP.(pf)		DC WORKING VOLTAGE	DC CURRENT (AMPS)	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MINIMUM NO LOAD INSERTION LOSS (dB) AT 25°C PER MIL-STD-220				
		-55° C TO 125° C				1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
27,000		100	10 A	10 G Ω	150	10	28	45	65	----

REVISION RECORD Original Release C.O. 19980403-8-02 ADDED AND REVISED NOTES. ADDED IR & DWV. S.M. 05-03-06 20060501-2-02	0		--TOLERANCES-- Unless Otherwise Specified	Title BUSHING STYLE EMI FILTER
	1		DECIMAL ± .031 [.79]	
			ANGLES ± 	Drawn S.M. 04-06-98
			TUSONIX TUCSON, ARIZONA	Approved J.Mc. 04-06-98
				A4402-060

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4402-060LF](#)