


CTX17-18765

Coupled power inductor



Product features

- 10 mm x 10 mm footprint surface mount package in a 4.0 mm height
- High current 2-phase inductor
- Ferrite core material

Applications

For exclusive use with Maxim® Multi-phase controllers

Environmental data

- Storage temperature range (component): -40 °C to +125 °C
- Operating temperature range: -40 °C to +125 °C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 (latest revision) compliant



Maxim® is a registered trademark of Maxim Integrated Devices, Inc.


Product specifications

Part Number ⁶	Inductor Phases	Functional Specifications				Test Specifications			
		Rated Inductance (nH) ¹	I_{max} Peak per Phase (Adc) ¹	I_{rms} per Phase (Adc) ⁵	OCL (nH) ²		SCL (nH) ³	FLL for SCL (nH) ⁴	DCR (m Ω) $\pm 8\%$ @ 20°C
					(1-4)	(2-3)			
CTX17-18765-R	2	50	55	33	200 $\pm 20\%$		100 $\pm 20\%$	64 min.	0.252
CTX17-18765-F	2	50	55	33	200 $\pm 20\%$		100 $\pm 20\%$	64 min.	0.252

1. The rated inductance per phase is determined by Maxim testing and circuit design. Additional information can be provided by contacting Maxim.
2. Open Circuit Inductance (OCL) Test Parameters: 100 kHz, 0.1 V_{rms}, 0.0 Adc, @ +25 °C
3. Short-Circuit Inductance (SCL) Test Parameters: 100 kHz, 0.1 V_{rms}, 0.0 Adc, @ +25 °C
4. Full Load Inductance (FLL) for (SCL), 100 kHz, 0.1 V_{rms}, 55 Adc, @ +25 °C
5. I_{rms} DC current per phase that will cause a 40°C temperature rise without core loss at +25 °C ambient. It is recommended the temperature not exceed +125 °C under worse case operating conditions verified in the end application.


6. This device is licensed for use only when incorporated within a voltage regulator employing power regulating devices manufactured by Maxim Integrated Devices. No license is granted expressly or by implication to use this device with power regulating devices manufactured by any company other than Maxim.

Dimensions- mm




Part marking: CTX17-18765, wwilly= date code, R= revision level
Part marking -F version: 17-18765-F, wwilly= date code, R= revision level
Pad layout tolerances ± 0.1 mm
Soldering surfaces to be coplanar within 0.1016 mm
Do not route traces or vias underneath the inductor

Packaging information - mm




Supplied in tape and reel packaging, 1000 parts per 13" diameter reel.

Temperature rise vs total loss



Inductance characteristics



Solder Reflow Profile




Table 1 - Standard SnPb Solder (T_p)

Package Thickness	Volume mm^3 <350	Volume mm^3 ≥ 350
<2.5mm	235°C	220°C
$\geq 2.5mm$	220°C	220°C

Table 2 - Lead (Pb) Free Solder (T_p)

Package Thickness	Volume mm^3 <350	Volume mm^3 350 - 2000	Volume mm^3 >2000
<1.6mm	260°C	260°C	260°C
1.6 – 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Reference JDEC J-STD-020

Profile Feature	Standard SnPb Solder	Lead (Pb) Free Solder
Preheat and Soak		
• Temperature min. (T_{smin})	100°C	150°C
• Temperature max. (T_{smax})	150°C	200°C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 Seconds	60-120 Seconds
Average ramp up rate T_{smax} to T_p	3°C/ Second Max.	3°C/ Second Max.
Liquidous temperature (T_L)	183°C	217°C
Time at liquidous (t_L)	60-150 Seconds	60-150 Seconds
Peak package body temperature (T_p)*	Table 1	Table 2
Time (t_p)** within 5 °C of the specified classification temperature (T_c)	20 Seconds**	30 Seconds**
Average ramp-down rate (T_p to T_{smax})	6°C/ Second Max.	6°C/ Second Max.
Time 25°C to Peak Temperature	6 Minutes Max.	8 Minutes Max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

** Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
www.eaton.com/electronics

© 2017 Eaton
All Rights Reserved
Printed in USA
Publication No. 4418 BU-SB11894
June 2017

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Eaton:](#)

[CTX17-18765-R](#)